



COMPONENTS	FUNCTION	LOCATION	CONTACTS
1MC	MOTOR CONTACTOR	12	1,3
1PS	PRESSURE TRANSDUCER	18	
H-O-A	HAND/OFF/AUTO SELECTOR SWITCH	12	
MCP	MOTOR CIRCUIT PROTECTOR	1,3	
PS	POWER SUPPLY	13	

**NOTES:**

3. FOR H-O-A SWITCH:  
H-O-A SWITCH CONNECTIONS SHOWN WHEN DOOR IS OPENED AND IN AUTO POSITION.
4. FOR FIELD WIRING:  
4-a) USE COPPER WIRING ONLY EXCEPT AT TERMINALS MARKED CU-AL, 60°C FOR TERMINALS RATED LESS THAN 100 AMPS.

OPTIONS LIST - OPTIONS MARKED WITH AN "X" ARE INCLUDED													
C	C	E	H	L	M	P	R	S	U	V	X	Y	Z



METRON  
Division of Hubbell-ICD, Inc.  
4301 Cheyenne Drive Archdale, N.C. 27263

LANGR	HOLE	ANGLES
0.X = .000	PUNCH	DIMEN.
0.XX = .005	±.005	± 1°
0.XXX = .020	±.010	
0.XXXX = .060	> .50	UNDIM.
	REAM SPECIFIED	90 ±.2

STANDARD SCHEMATIC DIAGRAM  
MP15 MICRO JOCKEY PUMP CONTROLLER  
SINGLE PHASE



DATE: 10/17/2014 DR. DAMA CK. APPR.

DRG. NO.  
1 OF 1 HCMP15S1P