


ALT. SOURCE
POWER OPERATOR




FRONT VIEW

PRESSURE CONNECTION
1/2" N.P.T - FEMALE

.50 [12] DIA.
MOUNTING HOLES


DRAIN



BOTTOM VIEW


2.5 [64]
TYP.

CIRCUIT BREAKER/
ISOLATION SWITCH
OPERATOR



SIDE VIEW

PILOT DEVICE DETAIL



LOCATED ON
TRANSFER SWITCH DOOR

NOTES:

ALL DIMENSIONS IN INCHES
AND MILLIMETERS ([])

VOLTAGE	HORSEPOWER
200V	75-125 HP.
208V	100-150 HP.
230V	100-150 HP.
380V, 415V	150-250 HP.
460V	200-300 HP.

DRAWN	/K	11-23-04	<p>METRON A Division of: Hubbell ICD, Inc. 4301 Cheyenne Dr., Archdale, NC 27263</p>
CHECK	RL	11-23-04	
APPD	77.7	11-23-04	
ENCLOSURE DIMENSIONS MODEL MP300 W/TRANSFER SWITCH 64" CABINET ELECTRIC FIRE PUMP CONTROLLER			OPTIONS: CD33806D
SCALE			N.T.S. SHEET 1 OF 1