



NOTES:

1. MINIMUM CLEARANCE FROM REAR OF CONTROLLER TO ANY WALL MUST BE 60.0 INCHES OR 152.4 CENTIMETERS.
2. SEE DRAWING CD31770 FOR LOW VOLTAGE DOOR COMPONENT LAYOUT.
3.  = RECOMMENDED CONDUIT ENTRY LOCATIONS.
4. ALL DIMENSIONS ARE SHOWN IN INCHES AND CENTIMETERS ([]).

LEGEND:

1. 1T FIELD TERMINALS
2. CT1, CT2 AND CT3 AND LOAD CONNECTION TERMINALS
3. LINE CONNECTION TERMINALS
4. PRESSURE SWITCH
5. EMERGENCY START HANDLE
6. DISCONNECT/INTERLOCK HANDLE
7. LOW VOLTAGE DOOR (SEE NOTE 2)

DRAWN	J.E. (REDRAWN)	10-27-95		METRON, INC. DENVER, CO.
CHECK	X.A.	10-31-95		
APPD	R.L.	10-31-95		
ENCLOSURE LAYOUT MODEL MV600, MED. VOLTAGE, (2300-7200V) ELECTRIC FIRE PUMP CONTROLLER				OPTIONS: NONE CD31769J
SCALE 1/12				SHEET 1 OF 1