


OPERATOR
INTERFACE
DEVICE/OID




FRONT VIEW

PRESSURE CONNECTION
1/2" N.P.T - FEMALE

2.5
[64]

CIRCUIT BREAKER/
ISOLATION SWITCH
OPERATOR

LOCKING
DOOR
HANDLE



EMERGENCY
START
OPERATOR

59.0
[1499]

2.50 [63.5] Ø
HOLES FOR PIPE
ENTRANCE
TYP (2)
TYP ALL LEGS

6.00
[152.4]


12.0
[305]

3.00
[76.2]

8.00
[203.2]


SIDE VIEW

.50 [12] DIA.
MOUNTING HOLES



BOTTOM VIEW

PILOT DEVICE DETAIL




NOTES:

ALL DIMENSIONS IN INCHES
AND MILLIMETERS ([])

RESISTOR ENCLOSURE RATING
TO BE A MAXIMUM TYPE 2.

HORSEPOWER	"X" DIMENSION
75-100 HP.	15.0 [381]
125-150 HP.	21.0 [533]

DRAWN	/K	11-17-04	 METRON A Division of: Hubbell ICD, Inc. <small>4301 Cheyenne Dr., Archdale, NC 27263</small>
CHECK	RA	11-17-04	
APPD	77.7	11-17-04	
ENCLOSURE DIMENSIONS MODEL MP400 32" CABINET ELECTRIC FIRE PUMP CONTROLLER			OPTIONS: CD33773C SCALE N.T.S. SHEET 1 OF 1