


SINGLE PHASE
INCOMING LINE



NOTES

- 1 - Incoming line terminals are provided to accommodate 125% of motor full load current per NFPA-20, Article 6-3.4, and NFPA-70 Tables 430-150 and 310-16. Copper (CU) wire is recommended.
- 2 - For correct field wire sizing, refer to the National Electrical Code, NFPA-70.

PRESSURE SYSTEM
CONNECTION
1/2" NPT

EXTERNAL CONTROL WIRE #14 AWG MINIMUM RECOMMENDED.
FOR STANDARD JOCKEY FIRE PUMP CONTROLLER
SCHEMATIC DIAGRAM, SEE DWG. NO. HCJ601AS001.



CONTROLLED DOCUMENT

This document is the property of Hubbell Industrial Controls, Inc., and may be reproduced for personal use only. Changes may be made only by Hubbell Industrial Controls, Inc.

E				M/L NO.	HJ601 STANDARD FIELD CONNECTIONS
D				MOTION:	PRESSURE MAKE UP (JOCKEY) FIRE PUMP CONTROLLER
C				REF.	110-120 VOLTS-AC, 60 HZ., SINGLE PHASE
B	04/27/11	DAMA		CADD NO. HCJ601AF001	DATE 11/05/10
A	12/01/10	DAMA		DR. JR	CK.
Rev.	DATE	BY			APPR.



Hubbell Industrial Controls, Inc.
4301 Cheyenne Drive, Archdale, N.C. 27263