





The Path Lighters 3091 / 3095 Installation Instructions



WARNING: Fixtures must be grounded in accordance with local codes or the National Electrical Code. Failure to do so may result in serious personal injury.



SAFETY WARNING: Lighted lamp is HOT! High temperature lenses can burn feet, hands or objects inadvertent-ly placed on top of fixtures. Do not touch hot lens, guard or enclosure.

To maintain light efficiency and prevent fixture overheating, lenses must be kept clean and free of dirt, dust, leaves, trash and mineral deposits from water.

KEEP THIS SHEET FOR FUTURE REFERENCE.

Tools Required:

☐ ¾16" Allen Wrench

□ RTV Silicone Sealant

□ Silicone Grease

INSTALLATION INSTRUCTIONS:




Make certain the electrical supply is **OFF** before starting fixture installation.


- Dig adequate hole for fixture. The fixture is designed to be mounted in a semi-recessed position. Grade level should slope away from fixture to avoid standing water whenever possible. Install a barrier frame to isolate fixture and provide a trim edge for landscaping.
- 2. Remove cover screws, cover, lens, and light shield.
- 3. Remove socket by loosening the two screws securing socket plate. Rotate plate clockwise to large openings in key slots and pull socket and leads from fixture housing.
- 4. Install unit to conduit system. After connections are made, seal around all wires and conduits entering or leaving the fixture (inside only) with RTV silicone sealant to prevent moisture from entering the fixture through the conduit system. Conduit drains are also recommended.
- 5. Attach fixture leads to circuit leads observing polarity, i.e. green-to-ground, white-to-common, and black-to-voltage.
- 6. Reassemble socket plate to fixture housing.
- 7. Install lamp of type and wattage shown on chart below (use A-21 bulb for lower fixture brightness).
- 8. Before replacing lens, orient 180° light shield to proper position. The shield may be trimmed or removed for up to 360° illumination.
- Install lens and cover. Make sure gasket surfaces are clean and check for proper seating of lens before tightening fixture cover screws. Coat screw threads with silicone grease and tighten evenly to insure uniform gasket pressure.

LAMP INFORMATION		
Cat. No.	Lamp Type	Max.Watts
3091	Incandescent A-21	100
3095	Fluorescent *F9DTT/27K	9

Lamp Warning:

The H.I.D. / Fluorescent fixtures utilize a lamp that may contain mercury. For information on disposal of lamp, go to website: www.lamprecycle.org





3095

Revised 7/16/10 ECN 100715008 Status 9 Part No. 95404

The Path Lighters - 3091 / 3035 Installation Instructions

KIM LIGHTING LIMITED WARRANTY

When installed in accordance with Kim Installation Instructions and accepted trade practices, the following shall apply:

General Product Limited Warranty Coverage

All material and component parts used in the manufacture of Kim Products, are warranted to be free from defects of material and/or workmanship for a period of 1 year from date of sale, with the following exceptions:

Auxiliary Equipment

All auxiliary equipment (such as lamps, ballasts, and transformers) provided by and/or included in Kim Products shall carry the component manufacturer's warranty.

Copper and Bronze Landscape Components

Copper and Bronze Landscape fixture components shall be warranted against defects of material and/or workmanship, and failure due to corrosion, for a period of 25 years from date of sale.

Composite In-Grade Components

Composite In-Grade fixture components installed below grade, shall be warranted against defects of material and/or workmanship, and failure due to corrosion, for a period of 7 years from date of sale.

Aluminum Landscape Components

Aluminum Landscape fixture components not in direct contact with soil, shall be warranted against defects of material and/or workmanship for a period of 3 years from date of sale. Aluminum fixture components in direct contact with soil shall be warranted from defects of material and failure from corrosion for a period of 1 year from date of sale.

Limit of Liability and General Conditions

Only products which are installed, used and maintained in accordance with applicable Kim instructions, specifications and accepted trade practices, are covered by the Kim Warranty. During the warranty period, with proof of purchase, Kim will repair or replace with the same or similar product, at Kim's option, without charge. Labor costs are the owner's responsibility and are excluded from this warranty. This warranty is void if the product is modified, tampered with, misapplied, poorly installed, improperly maintained, or subjected to abnormal conditions.

Repair or replacement as provided under this warranty is the exclusive remedy of the purchaser. This warranty is in lieu of all other warranties, expressed or implied, including any implied warranty of fitness for a particular application. Kim Lighting shall not be liable to the purchaser for indirect or consequential damages.



