

Introduction

This is a quick guide for the AccelTex folding mast mount. This install goes over the steps of putting the mount together in order to install the wireless solution. Once the overall setup is put together the height of it can be adjusted.

This product is intended for dry, flat, horizontal surfaces and should be properly secured depending on the specific environment

ATS-RDMM-16

Parts List

- 1 ATS-NPRM-TEMPEVENT-3.0 Base mount
- 2 Side supports (Included in base mount)
- 4 wing nuts (Included in base mount)
- 1 ATS-MST20-TEMPEVENT-3.0 Telescopic Mast



Step 1

Mount should be received as in the picture after unpacking with an adjustable height mast (not included in the picture). Please inspect all components are in the package. Overall setup is put together the height of it can be adjusted.



Step 2

Ensure 2 side supports are inside the tube.



Step 3

Release the folding tension cable and lay out the pieces to ensure all parts are included.



Step 4

Place the side supports as shown in the picture and tighten the wing nuts for safety.



Step 5

Place the bigger diameter end mast side on the base mount.



Step 6

Secure the base using weights (e.g. cinder blocks, sand bags, etc.) or other anchors.

How the mount is secured should be based on the specific environment the Mast Mount is assembled in.



Step 7

Use levelers to adjust desired height of mast.

