



**Parts List for Electric (AC)
CHANCE® Series 90
1,000-lb. Capstan Hoists**

ITEM NUMBER	DESCRIPTION	PART NUMBER	C308-1170 (115V)	C308-1171 (230V)
01	Motor Ass'y Complete (115 VAC)	T308-0868	1	—
	Motor Ass'y Complete (230 VAC)	T308-0869	—	1
01a	Cord, Motor	P308-0047	1	1
01b	End Cap	P308-0699	1	1
01c	Rectifier Bridge (not shown)	P308-0462	1	1
01d	Armature Ass'y 115V (not shown) includes gear	T308-0941	1	—
	Armature Ass'y 230V (not shown) includes gear	T308-0942	—	1
01e	Housing w/Magnets	P308-0722	1	1
01f	Brush End Housing	P308-0723	1	1
01g	Bearing, Brushend (not shown)	P308-0724	1	1
01h	Brush Plate Ass'y (not shown) (115V)	P308-0725	1	—
	Brush Plate Ass'y (not shown) (230V)	P308-0882	—	1
01i	Brush (not shown) (115V)	P308-0726	2	—
	Brush (not shown) (230V)	P308-0883	—	2
01j	Spring, Brush (not shown)	P308-0727	2	2
01k	Preload Spring, Armature (not shown)	P308-0728	1	1
02	Gear, Ring (74 Teeth)	P308-1341	1	1
03	Pin, Center	P308-1226	1	1
04	Washer, Thrust	P308-1029	3	3
05	Carrier Ass'y, 1st	E308-1413	1	1
06	Carrier Ass'y, 2nd	E308-1409	1	1
07	Shaft, Output Ass'y	E308-1424	1	1
08	Bearing	P316-0299	2	2
08a	Race, Bearing, in Housing (not shown)	P316-0300	2	2
09	Spacer Bearing	P308-1025	1	1
10	Housing, Output	P308-1028	1	1
11	Seal, Nilos	P316-0298	1	1
12	Washer, 2 ³ / ₈ " dia.	P308-0287	1	1
13	Lockwasher, 1/2"	P001-0994	1	1
14	Bolt, 1/2" x 1 1/4", GR5	P001-1521	1	1
15	Key	P308-1157	1	1
16	Bolt, Socket Head, 1/4" x 1 1/2"	P001-1542	4	4
17	Capstan Drum	P308-1327	1	1
18	Warning Label (115V)	P308-0832	1	—
	Warning Label (230V)	P308-0839	—	1
19	Grease, Gear	S12106	4 oz.	4 oz.