

**Surface Mount, Medium Base, Pony Cleat Incandescent  
Lamp-holder Wiring Instructions**

Cat. No.	Strip Length	Wire Size
RL 152 White Porcelain & RL 153 Black Plastic	1/2" [12.7]	No. 14-12 AWG 90° C min

- **NOTICE:** For installation by a qualified electrician in accordance with national and local electrical codes and included instructions.
- **CAUTION: RISK OF ELECTRIC SHOCK.**
  - Turn off power at the breaker before installing.
  - Verify that the device type and rating are suitable for the application.
  - Use Solid Copper Wire ONLY.
    - **Note: When using stranded conductor, twist strands to prevent loose strands when applying torque to terminal screw.**
    - **Note: When using stranded conductor, do not tin the leads.**
- **CAUTION:** In order to maintain correct polarity, the black conductor is terminated at the brass colored screw and the white conductor to the white/silver colored screw.
- Strip each conductor approximately 1/2" (Fig.1), form a loop and then wrap 3/4 turn under the head of the screw with free strip end positioned in clockwise direction ensuring the conductor is securely under the head of the screw (Fig.2).




Fig.1



Fig. 2

- While maintaining slight tension on the conductor, tighten each terminal screw to a torque of 7 - 9 in. lbs [.8 -1.0 Nm].

Wiring Device-Kellems  
Hubbell Incorporated (Delaware)  
Shelton, CT 06484, 1-800-288-6000

www.hubbell-wiring.com  
PD2488 Rev. 08/11