

## **RL124H Insulation Piercing Termination 660W 250V Medium Base Socket with Hook Wiring Instructions**

- **NOTICE:** For installation by a qualified electrician in accordance with national and local electrical codes and included instructions.
- **NOTICE:** For temporary use only.
- **CAUTION: RISK OF ELECTRIC SHOCK.**
  - Turn off power at the breaker before installing.
  - Verify that the device type and rating are suitable for the application.
  - Use #14 AWG Stranded Copper Thermoplastic Wire ONLY.
- Lay the insulated conductor directly onto the appropriate piercing pin.
  - Ribbed side is Neutral and is applied to the white/silver colored pin.
  - The smooth side is Hot and is applied to the brass colored pin.
- Rotate the lever clockwise till it has snapped into its fully locked position forcing the piercing pins through the conductor's insulation.

Wiring Device-Kellems  
Hubbell Incorporated (Delaware)  
Shelton, CT 06484  
1-800-288-6000  
[www.hubbell-wiring.com](http://www.hubbell-wiring.com)

PD2491 Rev. 10/11