

RL124 660W 600V Medium Base Socket with Pigtail Leads Wiring Instructions

- **NOTICE:** For installation by a qualified electrician in accordance with national and local electrical codes and included instructions.
- **NOTICE:** For temporary use only.
- **CAUTION: RISK OF ELECTRIC SHOCK.**
 - Turn off power at the breaker before installing.
 - Verify that the device type and rating are suitable for the application.
 - Use #14 – 12 AWG Copper Wire ONLY.
 - Note: When using stranded conductor, twist strands to prevent loose strands when securing with wire nuts.
 - Note: When using stranded conductor, do not tin the leads.
- Remove the pre-separated insulation from the end of the leads.
Identify Black leads and White leads of main circuit and connect to black and white leads of the pigtail socket in order to maintain polarity.
- Twist bare leads onto circuit leads and secure with appropriately sized wire nuts.

Wiring Device-Kellems
Hubbell Incorporated (Delaware)
Shelton, CT 06484
1-800-288-6000
www.hubbell-wiring.com

PD2492 Rev. 10/11