

Medium Base Prefocus HID Incandescent Bayonet Socket 1200W, 250V Wiring Instructions

Cat. No.	Strip Length	Wire Size
RL3742	1/2" [12.7]	No. 14 -12 AWG 90° C min

- **NOTICE:** For installation by a qualified electrician in accordance with national and local electrical codes and included instructions.
- **CAUTION: RISK OF ELECTRIC SHOCK.**
 - Turn off power at the breaker before installing.
 - Verify that the device type and rating are suitable for the application.
 - Use Copper Wire ONLY.
 - Note: When using stranded conductor, twist strands to prevent loose strands when tightening the terminal screw.
 - Note: When using stranded conductor, do not tin the leads.
- **CAUTION:** In order to maintain correct polarity, the black conductor is terminated at the brass colored screw and the white conductor to the white/silver colored screw.
- Strip each conductor approx. 1/2" [12.7] (Fig.1), form a loop and then wrap 3/4 turn under the head of the screw ensuring the conductor is securely under the head of the screw (Fig. 2).



Fig. 1



Fig. 2

- While maintaining slight tension on the conductor, tighten each terminal screw 10-12 lbf-in (1.1 – 1.4 Nm).

Wiring Device-Kellems
Hubbell Incorporated (Delaware)
Shelton, CT 06484
1-800-288-6000
www.hubbell-wiring.com

PD2493 Rev. 10/11