

TURNER BEARTRAP™ 1-WAY SWITCHES

TU-1TS2 ALUMINUM 1-WAY SIDE BREAK SWITCHES RATINGS 38-170kV AND 600-2000A

KEY BENEFITS

- Speed Independent operation—can be closed either fast or slow
- Reverse-loop, silver-plated copper jaw contacts—employ the natural repulsion of magnetic fields moving in opposite directions to exert holding forces against the blade edges
- Anti-Rollover Device—The BearTrap Switch from Turner employs a patented ramp and pin to securely position the blade in the jaw.
- Blade Position Indicator—High visibility stickers provide positive indication of the switch being open or closed. They also have high UV protection and come standard on every switch.
- Leveling —Leveling screws are provided on the movable and stationary insulator mounting flange for alignment of the insulator stacks. Three bolts are also on the jaw end for small final adjustments.

