



HPS VERSA-CRIMP™ TOOLS

ANDERSON™

BENEFITS

- One tool covers an entire range
- No dies or die sets required; simplified tooling sets
- Hand tools now have a 2-stage pump for quicker closure of the nibs and an overall faster installation
- Battery powered tools are now powered by a lithium-ion battery
- 360 degree rotatable heads for ease of use
- Repair kits are available for all tools



CATALOG NO.	VC6FTSP or VC7FTSP	VC63SP or VC7SP	VCBP6FT	VCBP63
DESCRIPTION	Manual Crimping Tool	Manual Crimping Tool	Battery Powered Crimping Tool	Battery Powered Crimping Tool
CONDUCTOR RANGE	#10-750 MCM Al/Cu or Cu Only	#10-750 MCM Al/Cu or Cu Only	#10-750 MCM Al/Cu	#10-750 MCM Al/Cu



CATALOG NO.	BP18CC129ACSR	VC6FTRSP or VC7FTRSP	VC6RSP or VC7RSP
DESCRIPTION	Battery Powered ACSR Cutting Tool	Remote Head Crimping Tool	Remote Head Crimping Tool
CONDUCTOR RANGE	Ranges up to: 1.29" Al/Cu cable, 1/2" Standard Guy Wire, 5/8" Ground Rods, 5/8" Soft Steel Bolts, 1113 MCM ACSR, 3/8" EHS Guy Wire, 1/2" Rebar	#10-750 MCM Al/Cu or Cu Only	#10-750 MCM Al/Cu or Cu Only



HUBBELL POWER SYSTEMS, INC.