

Clipping Hooks

For single and horizontally or vertically bundled conductors

Move conductors out of the work zone during line maintenance using hooks that attach easily to our tools. Three styles cover most applications. Vertical bundle hook includes Grip-All eye mount at the assembly bottom and 18" hook spacing for optimal handling.

Features

- Cast high-strength aluminum alloy
- Durable UV-resistant urethane lining
- Tamper-resistant galvanized shackle



PSC4013207 (left) & PSC4013206 (right)

Ordering Information

Product Number	Description	Length in. (cm)	Width in. (cm)	Conductor Capacity in. (cm)	WLL lb (kg)	Weight lb (kg)
PSC4013205	Standard Clipping Hook	14.5 (36)	5.5 (14)	1.762 (4)	6,500 (2,948)	7.8 (4)
PSC4013206	Heavy Duty Clipping Hook	17.0 (43)	8.0 (20)	3.0 (7)	12,000 (5,443)	19.5 (9)
PSC4013207	Vertical Bundle Clipping Hook	27.0 (68)	6.5 (16)	1.762 (4)	6,250 (2,834)	19.25 (9)