

Basic and Intelligent Power Distribution

- Single and three-phase power from 15A to 60A, available with and without breakers
- Multiple receptacle configurations and densities including standard NEMA, C13, and C19
- Intelligent PDUs feature advanced monitoring on LCD screen and built-in web browser to monitor and power cycle equipment remotely
- Stock available of common platforms
- Build to order program with typical lead time 3-5 weeks

Features and Benefits

- Superior locking of standard C-13 and C-19 plugs that prevent inadvertent disconnections
- Robotically-soldered connections for long-term problem-free powering operation
- Vertical solutions feature lowest published profile assuring maximum airflow, measuring only 2.18' wide, 2" deep for PDUs up to 60 amp, three-phase
- Available in standard black, white, red, and blue
- Assembled in North America
- 100% functional test before shipment

Power Distribution Types

- Basic - always-on reliable power
- Intelligent Switch Ready - Monitor outlet power and turn equipment on and off remotely through Hubbell switch cords

Online Intelligent Power Distribution Features and Benefits

- Power cycle equipment using Hubbell switching cords
- Monitor cabinet temperature and humidity with up to 4 environmental sensors per PDU, with provisions to set thresholds.
- Built-in web browser that displays total power consumption and temperature over last 2 weeks in graphical view
- Dual NICs allow multiple PDU monitoring and minimum use of IP addresses
- SNMP V3 encrypted



Basic and Intelligent Power Distribution

Ordering Information

Basic, Monitored, and Switch Ready Intelligent Power Distribution Unit, 72"

Catalog #	Nominal Voltage (VAC)	Input		Receptacle Group	Catalog #	Nominal Voltage (VAC)	Input		Receptacle Group
		Current (A)	Power Cord				Current (A)	Power Cord	
PV72BA20AA-XXXX	120V 1P	20	L5-20P	24 L5-20R	PV72ID50GD-XXXX	208V 3P	50	CS8365C	36 C13 & 6 C19
PV72IA20AA-XXXX	120V 1P	20	L5-20P	24 L5-20R	PV72BD50GE-XXXX	208V 3P	50	CS8365C	24 C13 & 12 C19
PV72BA30BA-XXXX	120V 1P	30	L5-30P	24 L5-20R	PV72ID50GE-XXXX	208V 3P	50	CS8365C	24 C13 & 12 C19
PV72IA30BA-XXXX	120V 1P	30	L5-30P	24 L5-20R	PV72BD50GF-XXXX	208V 3P	50	CS8365C	18 C13 & 18 C19
PV72BB20CC-XXXX	208V 1P	20	L6-20P	32 C13 & 4 C19	PV72ID50GF-XXXX	208V 3P	50	CS8365C	18 C13 & 18 C19
PV72IB20CC-XXXX	208V 1P	20	L6-20P	32 C13 & 4 C19	PV72BD60HD-XXXX	208V 3P	60	60309	36 C13 & 6 C19
PV72BB30DD-XXXX	208V 1P	30	L6-30P	36 C13 & 6 C19	PV72ID60HD-XXXX	208V 3P	60	60309	36 C13 & 6 C19
PV72IB30DD-XXXX	208V 1P	30	L6-30P	36 C13 & 6 C19	PV72BD60HE-XXXX	208V 3P	60	60309	24 C13 & 12 C19
PV72BC30EBD-XXXX	208V 3P	30	L21-30P	36 C13 & 6C19, 2 L5-20R	PV72ID60HE-XXXX	208V 3P	60	60309	24 C13 & 12 C19
PV72IC30EBD-XXXX	208V 3P	30	L21-30P	36 C13 & 6C19, 2 L5-20R	PV72BD60HF-XXXX	208V 3P	60	60309	18 C13 & 18 C19
PV72BD30FD-XXXX	208V 3P	30	L15-30P	36 C13 & 6 C19	PV72ID60HF-XXXX	208V 3P	60	60309	18 C13 & 18 C19
PV72ID30FD-XXXX	208V 3P	30	L15-30P	36 C13 & 6 C19	PV72BE20HG-XXXX	415V 3P	20	60309	36 C13 & 12 C19
PV72BD35GD-XXXX	208V 3P	35	CS8365C	36 C13 & 6 C19	PV72IE20HG-XXXX	415V 3P	20	60309	36 C13 & 12 C19
PV72ID35GD-XXXX	208V 3P	35	CS8365C	36 C13 & 6 C19	PV72BE30HH-XXXX	415V 3P	30	60309	30 C13 & 12 C19
PV72BD50GD-XXXX	208V 3P	50	CS8365C	36 C13 & 6 C19	PV72IE30HH-XXXX	415V 3P	30	60309	30 C13 & 12 C19
					PV72BE60HI-XXXX	415V 3P	60	60309	27 C19

Catalog Number Configurator

First 4 Char.		5th Char.		6th Char.		7th & 8th Char.		9th Char.		10th Char.		11th & 12th Char.		13th & 14th Char.		
Product description	Cat #	Intelligent option	Cat #	Volts & phase	Cat #	Amps	Cat #	Plug type	Cat #	Receptacles	Cat #	Cord length	Cat #	Cover color	Cat #	
Power Dist. Vertical 72"	PV72	Basic	B	1P 120	A	20	20	L5-20P	A	(24) 5-20R	A	6 Foot	6	Black*	(blank)	
				1P 208	B	30	30	L5-30P	B	(2) 5-20R	B		10 Foot	10	Blue	BL
		Intelligent	I	3P 208Y	C	35	35	L6-20P	C	(32) C13 & (4) C19	C				Red	RD
				3P 240D	D	50	50	L6-30P	D	(36) C13 & (6) C19	D				White	WH
				3P 415Y	E	60	60	L21-30P	E	(24) C13 & (12) C19	E					
								L15-30P	F	(18) C13 & (18) C19	F					
				CS8365C	G	(36) C13 & (12) C19	G									
				60309	H	(30) C13 & (12) C19	H									
				60309	I	(27) C19	I									

*Default color

Horizontal Basic Power Distribution Units

Catalog #	Description	Surge Protected	Size (Rack Units)	Input Current (A)	Power Rating (kW)	Input Power Cord	Output Receptacles	Circuit Protection	On/Off Switch
PH15A10	19" rack mount	No	1	15	1.4	10' w/ 5-15P Plug	(10) NEMA 5-15R	15A Breaker	No
PH15A10S	19" rack mount	No	1	15	1.4	10' w/ 5-15P Plug	(10) NEMA 5-15R	15A Breaker	Yes
PH20A10	19" rack mount	No	1	20	1.9	10' w/ 5-20P Plug	(10) NEMA 5-20R	20A Breaker	No
PH20A10S	19" rack mount	No	1	20	1.9	10' w/ 5-20P Plug	(10) NEMA 5-20R	20A Breaker	Yes
MCCPSS19	19" rack mount	Yes	1	15	1.4	10' w/ 5-15P Plug	(10) NEMA 5-15R	15A Breaker	Yes

Count on Hubbell, powering your trust for over 135 years



A proud member of the Hubbell family.

©2024 Hubbell Premise Wiring. All rights reserved. Hubbell and the Hubbell logo are registered trademarks or trademarks of Hubbell Incorporated. All other trademarks are the property of their respective owners. 40 Waterview Dr., Shelton, CT 06484 | www.hubbell.com/hubbellpremiwiring Phone 1-800-626-0005 | Fax 1-860-535-8328

EP-PREM-SF-EN-02049 | REV 04 2024