

HUBBELL Premise Wiring

Quick-Turn High-Performance Patch Cords

Hubbell's wide range of quality cords to make the final network connection

Our fiber cords are inspected and tested to the highest industry standards and come equipped with a full performance report. Our copper cords are manufactured with top quality components, tuned to the connectors and cable, and third party-tested for component compliance, creating a superior end-to-end system. We have a wide range of cords in stock and are able to support custom applications with quick-turn service.



FiberHubb™ Series Fiber Optic Patch Cords

Description	Cable Color	Length (meters)			
		1m	2m	3m	5m
Standard Duplex					
LC to LC, OM4	AQ	FDLC1MM	FDLC2MM	FDLC3MM	FDLC5MM
LC to LC, OS2	YL	FDLC1SM	FDLC2SM	FDLC3SM	FDLC5SM
Custom Duplex					
Riser					
LC to SC, OM4	AQ	DFHRCLCSCF1MM	DFHRCLCSCF2MM	DFHRCLCSCF3MM	DFHRCLCSCF5MM
LC to SC, OS2	YL	DFHRCLCSCS1SM	DFHRCLCSCS2SM	DFHRCLCSCS3SM	DFHRCLCSCS5SM
Plenum					
LC to LC, OM4	AQ	DFHPCLCLCF1MM	DFHPCLCLCF2MM	DFHPCLCLCF3MM	DFHPCLCLCF5MM
LC to SC, OM4	AQ	DFHPCLCSCF1MM	DFHPCLCSCF2MM	DFHPCLCSCF3MM	DFHPCLCSCF5MM
LC to LC, OM4	VL	DFHPCLCLCF1MVI	DFHPCLCLCF2MVI	DFHPCLCLCF3MVI	DFHPCLCLCF5MVI
LC to LC, OS2	YL	DFHPCLCSCS1SM	DFHPCLCSCS2SM	DFHPCLCSCS3SM	DFHPCLCSCS5SM
LC to SC, OS2	YL	DFHPCLCSCS1SM	DFHPCLCSCS2SM	DFHPCLCSCS3SM	DFHPCLCSCS5SM

Custom cords are available in Plenum or Riser in any length

Reversible High Density Fiber Optic Patch Cords

Reversible Push Pull, Plenum

Description	Cable Color	Length (meters)			
		1m	2m	3m	5m
LC to LC PushPull, OM4	AQ	HDFHPCLCPRPG4M1	HDFHPCLCPRPG4M2	HDFHPCLCPRPG4M3	HDFHPCLCPRPG4M5
LC to LC PushPull, OS2	YL	HDFHPCLCPRPSM1	HDFHPCLCPRPSM2	HDFHPCLCPRPSM3	HDFHPCLCPRPSM5

Simplex Fiber Optic Patch Cords

Riser

Description	Cable Color	Length (meters)			
		1m	2m	3m	5m
LCA to LCA, OS2	YL	SFHRCLCALCAS1SM	SFHRCLCALCAS2SM	SFHRCLCALCAS3SM	SFHRCLCALCAS5SM
LCA to SCA, OS2	YL	SFHRCLCASCAS1SM	SFHRCLCASCAS2SM	SFHRCLCASCAS3SM	SFHRCLCASCAS5SM
LCA to SC, OS2	YL	SFHRCLCASCAS1SM	SFHRCLCASCAS2SM	SFHRCLCASCAS3SM	SFHRCLCASCAS5SM
LC to LCA, OS2	YL	SFHRCLCLCAS1SM	SFHRCLCLCAS2SM	SFHRCLCLCAS3SM	SFHRCLCLCAS5SM
LC to LCA, OS2	YL	SFHRCLCLCS1SM	SFHRCLCLCS2SM	SFHRCLCLCS3SM	SFHRCLCLCS5SM
LC to SCA, OS2	YL	SFHRCLCSCAS1SM	SFHRCLCSCAS2SM	SFHRCLCSCAS3SM	SFHRCLCSCAS5SM
SCA to SCA, OS2	YL	SFHRCSASCAS1SM	SFHRCSASCAS2SM	SFHRCSASCAS3SM	SFHRCSASCAS5SM
SC to SCA, OS2	YL	SFHRCSASCAS1SM	SFHRCSASCAS2SM	SFHRCSASCAS3SM	SFHRCSASCAS5SM
SC to SC, OS2	YL	SFHRCSSCS1SM	SFHRCSSCS2SM	SFHRCSSCS3SM	SFHRCSSCS5SM

NEXTSPEED® Ascent Low Diameter Category 6A Copper Patch Cords

Nominal O.D. 0.186"; single pack; 24-piece bulk pack available up to 15' (add X24 to catalog no.)

Cable Color	Length (feet)							
	1'	3'	5'	7'	10'	15'	20'	25'
Black	HCL6ABK01	HCL6ABK03	HCL6ABK05	HCL6ABK07	HCL6ABK10	HCL6ABK15	HCL6ABK20	HCL6ABK25
Blue	HCL6AB01	HCL6AB03	HCL6AB05	HCL6AB07	HCL6AB10	HCL6AB15	HCL6AB20	HCL6AB25
Gray	HCL6AGY01	HCL6AGY03	HCL6AGY05	HCL6AGY07	HCL6AGY10	HCL6AGY15	HCL6AGY20	HCL6AGY25
Green	HCL6AGN01	HCL6AGN03	HCL6AGN05	HCL6AGN07	HCL6AGN10	HCL6AGN15	HCL6AGN20	HCL6AGN25
Orange	HCL6AOR01	HCL6AOR03	HCL6AOR05	HCL6AOR07	HCL6AOR10	HCL6AOR15	HCL6AOR20	HCL6AOR25
Pink	HCL6APK01	HCL6APK03	HCL6APK05	HCL6APK07	HCL6APK10	HCL6APK15	HCL6APK20	HCL6APK25
Purple	HCL6AP01	HCL6AP03	HCL6AP05	HCL6AP07	HCL6AP10	HCL6AP15	HCL6AP20	HCL6AP25
Red	HCL6AR01	HCL6AR03	HCL6AR05	HCL6AR07	HCL6AR10	HCL6AR15	HCL6AR20	HCL6AR25
White	HCL6AW01	HCL6AW03	HCL6AW05	HCL6AW07	HCL6AW10	HCL6AW15	HCL6AW20	HCL6AW25
Yellow	HCL6AY01	HCL6AY03	HCL6AY05	HCL6AY07	HCL6AY10	HCL6AY15	HCL6AY20	HCL6AY25

NEXTSPEED Low Diameter Category 6 Copper Patch Cords

Nominal O.D. 0.150"; single pack; 24-piece bulk pack available up to 15' (add X24 to Catalog Number)

Cable Color	Length (feet)							
	1'	3'	5'	7'	10'	15'	20'	25'
Black	HCL6BK01	HCL6BK03	HCL6BK05	HCL6BK07	HCL6BK10	HCL6BK15	HCL6BK20	HCL6BK25
Blue	HCL6B01	HCL6B03	HCL6B05	HCL6B07	HCL6B10	HCL6B15	HCL6B20	HCL6B25
Gray	HCL6GY01	HCL6GY03	HCL6GY05	HCL6GY07	HCL6GY10	HCL6GY15	HCL6GY20	HCL6GY25
Green	HCL6GN01	HCL6GN03	HCL6GN05	HCL6GN07	HCL6GN10	HCL6GN15	HCL6GN20	HCL6GN25
Orange	HCL6OR01	HCL6OR03	HCL6OR05	HCL6OR07	HCL6OR10	HCL6OR15	HCL6OR20	HCL6OR25
Pink	HCL6PK01	HCL6PK03	HCL6PK05	HCL6PK07	HCL6PK10	HCL6PK15	HCL6PK20	HCL6PK25
Purple	HCL6P01	HCL6P03	HCL6P05	HCL6P07	HCL6P10	HCL6P15	HCL6P20	HCL6P25
Red	HCL6R01	HCL6R03	HCL6R05	HCL6R07	HCL6R10	HCL6R15	HCL6R20	HCL6R25
White	HCL6W01	HCL6W03	HCL6W05	HCL6W07	HCL6W10	HCL6W15	HCL6W20	HCL6W25
Yellow	HCL6Y01	HCL6Y03	HCL6Y05	HCL6Y07	HCL6Y10	HCL6Y15	HCL6Y20	HCL6Y25

NEXTSPEED Ascent High Flex Standard Category 6A Copper Patch Cords

Nominal O.D. 0.233"; single pack; 24-piece bulk pack available up to 15' (add X24 to catalog no.)

Cable Color	Length (feet)							
	1'	3'	5'	7'	10'	15'	20'	25'
Black	HC6ABK01	HC6ABK03	HC6ABK05	HC6ABK07	HC6ABK10	HC6ABK15	HC6ABK20	HC6ABK25
Blue	HC6AB01	HC6AB03	HC6AB05	HC6AB07	HC6AB10	HC6AB15	HC6AB20	HC6AB25
Gray	HC6AGY01	HC6AGY03	HC6AGY05	HC6AGY07	HC6AGY10	HC6AGY15	HC6AGY20	HC6AGY25
Green	HC6AGN01	HC6AGN03	HC6AGN05	HC6AGN07	HC6AGN10	HC6AGN15	HC6AGN20	HC6AGN25
Orange	HC6AOR01	HC6AOR03	HC6AOR05	HC6AOR07	HC6AOR10	HC6AOR15	HC6AOR20	HC6AOR25
Pink	HC6APK01	HC6APK03	HC6APK05	HC6APK07	HC6APK10	HC6APK15	HC6APK20	HC6APK25
Purple	HC6AP01	HC6AP03	HC6AP05	HC6AP07	HC6AP10	HC6AP15	HC6AP20	HC6AP25
Red	HC6AR01	HC6AR03	HC6AR05	HC6AR07	HC6AR10	HC6AR15	HC6AR20	HC6AR25
White	HC6AW01	HC6AW03	HC6AW05	HC6AW07	HC6AW10	HC6AW15	HC6AW20	HC6AW25
Yellow	HC6AY01	HC6AY03	HC6AY05	HC6AY07	HC6AY10	HC6AY15	HC6AY20	HC6AY25

NEXTSPEED High Flex Standard Category 6 Copper Patch Cords

Nominal O.D. 0.224"; single pack; 24-piece bulk pack available up to 15' (add X24 to Catalog Number)

Cable Color	Length (feet)							
	1'	3'	5'	7'	10'	15'	20'	25'
Black	HC6BK01	HC6BK03	HC6BK05	HC6BK07	HC6BK10	HC6BK15	HC6BK20	HC6BK25
Blue	HC6B01	HC6B03	HC6B05	HC6B07	HC6B10	HC6B15	HC6B20	HC6B25
Gray	HC6GY01	HC6GY03	HC6GY05	HC6GY07	HC6GY10	HC6GY15	HC6GY20	HC6GY25
Green	HC6GN01	HC6GN03	HC6GN05	HC6GN07	HC6GN10	HC6GN15	HC6GN20	HC6GN25
Orange	HC6OR01	HC6OR03	HC6OR05	HC6OR07	HC6OR10	HC6OR15	HC6OR20	HC6OR25
Pink	HC6PK01	HC6PK03	HC6PK05	HC6PK07	HC6PK10	HC6PK15	HC6PK20	HC6PK25
Purple	HC6P01	HC6P03	HC6P05	HC6P07	HC6P10	HC6P15	HC6P20	HC6P25
Red	HC6R01	HC6R03	HC6R05	HC6R07	HC6R10	HC6R15	HC6R20	HC6R25
White	HC6W01	HC6W03	HC6W05	HC6W07	HC6W10	HC6W15	HC6W20	HC6W25
Yellow	HC6Y01	HC6Y03	HC6Y05	HC6Y07	HC6Y10	HC6Y15	HC6Y20	HC6Y25



A Hubbell brand

©2024 Premise Wiring. All rights reserved.
 Hubbell and the Hubbell logo are registered trademarks or trademarks of Hubbell Incorporated. All other trademarks are the property of their respective owners.
 40 Waterview Dr. Shelton, CT 06484