

# Power and AV Wall Boxes

## Wall Boxes

Power, data, interfaces and more will mount discretely behind the flat screen. Covers two piece are available in white or black. Supplied with mounting screws for wood or steel stud mounting, grounding screws, tie wraps, and rubber grommets. Two of the single gang knockouts has a 1" x 2" oblong internal knockout and can be used with the supplied grommets. The flush box installation allows flat panel displays and interactive "smart" boards to sit flush against walls with no dangling cords.

### Features

- Low voltage conduit feed-thru for connectorized cables with 1", 1-1/2" and 2" Knockouts
- 3/4" extension available for concrete block walls
- Two-piece paintable cover allows for better cable management
- Boxes Conforms to UL 62368-1:2019 Ed.3, Certified to CSAC22.2#62368-1:2019 Ed.3

## Wall Enclosure

2 and 4-Gang Flat Panel Television (FPTV) connection enclosure delivers high-density connectivity and power in the wall. This allows flat panel displays and interactive "smart" boards to sit flush against walls with no dangling cords. It quickly installs to studs or sheetrock without additional components or hardware

- Optional screw on cover reduces tampering
- cULus 1863 Listed

### Box Design and Mounting

- Flush against walls installation
- Sheet metal base white powder coat finish
- Accepts standard electrical boxes
- Integrated cable management
- Multiple device mounting options
- 1½ and 1¼ inch conduit knockouts
- Easily mounts to studs or sheetrock
- Easily replaceable receptacle
- Trim ring covers rough in



**HRWB25WHT with 2 Inch Low Voltage Feed-Through**



**HRWB25WHT**



**HRWB25WHT with HRW25BE075**



**NSAV124M**



**NSAV62M**



### Wall Boxes

Description	Height	Width	Depth	Cover Color	Catalog No.
Recessed 5-Gang wall box w/ 2" feed-thru	7.24" (183.8)	14.25" (362.0)	4.00" (141.6)	White	<b>HRWB25WHT</b>
HRWB25WHT replacement covers	8.34" (211.7)	15.50" (393.7)	0.16" (4.0)	White	<b>HRWB25WHTRC</b>
Recessed 5-Gang wall box w/ 2" feed-thru	7.24" (183.8)	14.25" (362.0)	4.00" (141.6)	Black	<b>HRWB25BLK</b>
HRWB25BLK replacement covers	8.34" (211.7)	15.50" (393.7)	0.16" (4.0)	Black	<b>HRWB25BLKRC</b>
HRWB25 series wall box 3/4" extension	7.47" (189.7)	14.50" (368.3)	0.75" (19.1)	Steel	<b>HRWB25BE075</b>

### Power Kits

Description	Color	Catalog No.
Standard power kit.	White	<b>NSOKPTR</b>
Surge protected power kit.	White	<b>NSOKPS</b>



IFP16W



NSOKPS

### AV Connectors and Plates

Description	Color	Catalog No.
1-Gang 6-Port Plate.	White	<b>IFP16W</b>
1-Gang Hubbell iSTATION Plate	White	<b>IMF1W</b>
Category 6 Jack	White	<b>HXJ6W</b>
HDMI Feed-Thru	White	<b>SFHC14W</b>



IMF1W



HXJ6W



SFHC14W

### FPTV Connection Enclosure

Description	Color	Catalog No.
2-Gang In-Wall enclosure.	White	<b>NSAV62M</b>
Steel cover for NSAV6 series.	White	<b>NSAV6C</b>
4-Gang In-Wall enclosure.	White	<b>NSAV124M</b>
Steel cover for NSAV12 series.	White	<b>NSAV12C</b>



NS801W



NSAV6C

HFCB designates Hubbell Premise Wiring branded cable jacket

### Power Kits

Description	Color	Catalog No.
Standard power kit.	White	<b>NSOKPTR</b>
Surge protected power kit.	White	<b>NSOKPS</b>



NSOKPS



SFHC14W

### AV Connectors and Plates

Description	Color	Catalog No.
1-Gang blank plate.	White	<b>P14W</b>
1-Gang decorator plate.	White	<b>P26W</b>



NSJ6W



A proud member of the Hubbell family.

©2023 Hubbell Premise Wiring. All rights reserved.  
 Hubbell and the Hubbell logo are registered trademarks  
 or trademarks of Hubbell Incorporated.  
 All other trademarks are the property of their respective owners.  
[hubbell.com/hubbellpremiawiring](http://hubbell.com/hubbellpremiawiring)  
 Phone 1-800-626-0005 | Fax 1-860-535-8328

EP-PREM-SF-EN-01084 | REV 06 2023