

8/10-Gang Recessed Floor Boxes

With maximum capacity in a small footprint, the 8/10-Gang box provides a uniform look with rectangular or round covers that are available in several finishes to complement existing décor. Electrical devices are mounted vertically and are mounted to the plate prior to securing it to the box. Four removable knockout plates allows for 2" conduit feed-thru allowing for simple installation of AV cables with pre-connectorized heads and specific bend radius requirements.

Features and Benefits

Box





- 3.75" deep wiring device chambers
- 14 gauge galvanized sheet metal
- Optional fusion-bonded, green epoxy paint for on-grade use
- 8/10- Gang floor boxes accept field installed metallic 2" threaded hubs and PVC hubs
- Patented PVC conduit adapters can be used on metal and PVC floor boxes—**CFBHUB200PVC** (2 in. feed-thru) and **CFBHUB125PVC** (1¼" feed-thru)
- Pre-pour and post-pour adjustment
- Labor saving, easy mount device plates

Cover

- Available in round and rectangular, recessed and furniture feed styles
- Rectangular covers- maximum static load of 1,500 lbs. with 2x safety factor
- Round covers- maximum static load of 1,000 lbs. with 2x safety factor
- Recessed covers open a full 180°
- Large hide-away cable egress doors
- Listed to UL 514A and UL Scrubwater compliant
- Die cast aluminum cover construction
- All covers are ADA compliant



8/10-Gang Floor Boxes

Style	Rectangular Cover		Round Cover	
				
Standard Box	CFB10G55E	-	CFB10G55RE	-
Corrosion-Resistant (On-grade)	-	CFB10G55CRE	-	CFB10G55RCRE
Recommended Pour Depth	6.00" (152.4)		6.25" (158.8)	
Min. Depth of Pour	5.50" (139.7)		6.25" (158.8)	



Rectangular Covers



Available finishes

Aluminum Powder Coat Black Powder Coat Brass Powder Coat Bronze Powder Coat Satin Nickel Powder Coat

Finish	Surface Cover Dimensions 11½ in. x 10 in.			Flush Cover Dimensions 10½ in. x 9 in.		
	Without Insert	With Insert	Furniture Feed ((2)1 in. & (2) 2 in. Plugs)	Without Insert	With Insert	Furniture Feed ((2)1 in. & (2) 2 in. Plugs)
Aluminum Powder Coat	610GCCVRALU	610GCCVREALUC	610GCCFFCVRALU*	610GTCVREALU	610GTCVREALUC	610GTFFCVRALU*
Black Powder Coat	610GCCVRBK	610GCCVRBKC	610GCCFFCVRBK*	610GTCVRBK	610GTCVRBKC	610GTFFCVRBK*
Brass Powder Coat	610GCCVRBRS	610GCCVRBRSC	610GCCFFCVRBRS*	610GTCVRBRS	610GTCVRBRSC	610GTFFCVRBRS*
Bronze Powder Coat	610GCCVRBRZ	610GCCVRBRZC	610GCCFFCVRBRZ*	610GTCVRBRZ	610GTCVRBRZC	610GTFFCVRBRZ*
Satin Nickel Powder Coat	610GCCVRNK	610GCCVRNKC	610GCCFFCVRNK*	610GTCVRNK	610GTCVRNKC	610GTFFCVRNK*

*For 8/10-gang box dual service, **CFB10FFDIVKIT** required with furniture feed covers. Purchased separately.



8 Inch Round Covers



Available finishes

Brushed Aluminum Black Powder Coat Brass Plated Bronze Plated Gray Powder Coat Satin Nickel Plated

Finish	Flush Surface	Furniture Feed (¾ in. and 2 in. Plugs)
Brushed Aluminum	CFBS1R8CVRALU	CFBS1R8FFCVRALU**
Black Powder Coat	CFBS1R8CVRBLK	CFBS1R8FFCVRBLK**
Brass Plated	CFBS1R8CVRBRS	CFBS1R8FFCVRBRS**
Bronze Plated	CFBS1R8CVRBRZ	CFBS1R8FFCVRBRZ**
Gray Powder Coat	CFBS1R8CVRGRY	CFBS1R8FFCVRGRY**
Satin Nickel Plated	CFBS1R8CVRNKL	CFBS1R8FFCVRNKL**



For 10-gang box dual service, **CFBS1R8FF10GDIVKIT required with Furniture Feed covers. Purchased separately.

Plates for use in SystemOne 8/10-Gang floor boxes

FB10MPREC	(1) Decorator opening	FB10MPDUP	(1) Duplex opening
FB10MPBNK	1-gang blank plate	FB10MPKEY	(1) Opening with Hubbell 6-port frame for keystone jacks
FB10MPTRAC	(2) Openings for (6) Ortronics TracJack®	FB10MPFT	Cable feed through with bushing
FB10MP2A	Two Gang Plate Style Decorator openings	FB10MP2E	Two Gang Plate Style Duplex openings
FB10TLX	(1) Simplex opening 1.40 in. diameter	FB10TLA	(1) Twist-Lock® opening 1.60 in. diameter
FB10MP2B	(6) 1U Hubbell iStation modules	FB10MPMAAP	Siemon CT Series
FB10MPAAP	(4) Extron® AAP openings		
FB10TLY	Three Gang Plate Style (2) Simplex opening 1.40 in. diameter	FB10TLB	Three Gang Plate Style (3) Twist-Lock® opening 1.60 in. diameter
FB10MP3GAPP	(1) Opening for appliance receptacle, requires 2-gang industry plate for trim out		
FB10TLC	Five Gang Plate Style (3) Simplex opening 1.40 in. diameter	FB10TLZ	Five Gang Plate Style Twist-Lock® opening 1.60 in. diameter
FB10MPNEMA2XG#	(2) 2-gang. Meets NEMA spacing. Ideal for Crestron® DM —TX product and power. Ships with low voltage divider.	FB10MPNEMA4G#	(4) Single service openings utilizing NEMA wallplate. (No low voltage divider option.)

#Use with FB10MPNEMA2XG and/or FB10MPNEMA4G for 8-gang configuration.

Extron® is a registered trademark of Extron Electronics. Crestron® is a registered trademark of Crestron Electronics, Inc. TracJack®, Series II® and Ortronics® are registered trademarks of Ortronics/Legrand.



A proud member of the Hubbell family.