

Wall Boxes

Power, data, interfaces and more will mount discretely behind the flat screen. Covers two piece are available in white or black. Supplied with mounting screws for wood or steel stud mounting, grounding screws, tie wraps, and rubber grommets. Two of the single gang knockouts has a 1" x 2" oblong internal knockout and can be used with the supplied grommets. The flush box installation allows flat panel displays and interactive "smart" boards to sit flush against walls with no dangling cords.

FEATURES

- \bullet $\,$ Low voltage conduit feed-thru for connectorized cables with 1", 1-1/2" and 2" Knockouts
- 3/4" extension available for concrete block walls
- Two-piece paintable cover allows for better cable management
- Boxes Conforms to UL 62368-1:2019 Ed.3. Certified to CSAC22.2#62368-1:2019 Ed.3

Wall Enclosure

2 and 4-Gang Flat Panel Television (FPTV) connection enclosure delivers high density connectivity and power in the wall. This allows flat panel displays and interactive "smart" boards to sit flush against walls with no dangling cords. It quickly installs to study or sheetrock without additional components or hardware.

- Optional screw on cover reduces tampering
- cULus 1863 Listed

BOX DESIGN AND MOUNTING

- Flush against walls installation
- Sheet metal base white powder coat finish
- Accepts standard electrical boxes
- Integrated cable management
- Multiple device mounting options
- 1½ and 1¼ inch conduit knockouts
- Easily mounts to studs or sheetrock
- Easily replaceable receptacle
- Trim ring covers rough in



HRWB25WHT with 2 Inch Low Voltage Feed-Through



HRWB25WHT



HRWB25WHT with HRW25BE075



NSAV124M



NSAV62M





WALL BOXES



Description	Height	Width	Depth	Cover Color	Catalog Number
Recessed 5-Gang wall box w/ 2" feed-thru	7.24" (183.8)	14.25" (362.0)	4.00" (141.6)	White	HRWB25WHT
HRWB25WHT replacement covers	8.34" (211.7)	15.50" (393.7)	0.16" (4.0)	White	HRWB25WHTRC
Recessed 5-Gang wall box w/ 2" feed-thru	7.24" (183.8)	14.25" (362.0)	4.00" (141.6)	Black	HRWB25BLK
HRWB25BLK replacement covers	8.34" (211.7)	15.50" (393.7)	0.16" (4.0)	Black	HRWB25BLKRC
HRWB25 series wall box 3/2" extension	7.47" (189.7)	14.50" (368.3)	0.75" (19.1)	Steel	HRWB25BE075

POWER KITS



Description	Color	Catalog Number
Standard power kit.	White	NSOKPTR
Surge protected power kit.	White	NSOKPS





AV CONNECTORS AND PLATES

Description	Color	Catalog Number
1-Gang 6-Port Plate.	White	IFP16W
1-Gang Hubbell iSTATION Plate	White	IMF1W
Category 6 Jack	White	HXJ6W
HDMI Feed-Thru	White	SFHC14W

IFP16W

NSOKPS





IMF1W

SFHC14W

FPTV CONNECTION ENCLOSURE

Description	Color	Catalog Number
2-Gang In-Wall enclosure.	White	NSAV62M
Steel cover for NSAV6 series.	White	NSAV6C
4-Gang In-Wall enclosure.	White	NSAV124M
Steel cover for NSAV12 series.	White	NSAV12C





NS801W

NSAV6C

POWER KITS

Description	Color	Catalog Number
Standard power kit.	White	NSOKPTR
Surge protected power kit.	White	NSOKPS

Color

White

White

Catalog Number

P14W

P26W





NSOKPS

NSJ6W

For additional options and technical information, please see our full line catalog.



Description

1-Gang blank plate.

1-Gang decorator plate.

A proud member of the Hubbell family.

AV CONNECTORS AND PLATES