



## Hubbell-PRO IEC pin & sleeve devices with NPT threaded back housing

### NOW ACCEPT LIQUIDTIGHT FITTINGS

Hubbell-PRO IEC pin & sleeve maximize performance and installation efficiency, minimizing the total cost of ownership.

- Value engineered for price/performance balance
- Integral NPT-threaded back housing directly accepts liquidtight fittings
- All 30A and 32A devices feature maintenance-free screwless terminations
- Glandless water ingress protection on the cable side of the device
- Dual rated versions available, where applicable



### Improve installation time by over 80%

The ONLY UL-approved screwless terminations for 30/32A IEC 60309 pin & sleeve

Hubbell's EdgeConnect™ technology terminates connections faster. Just insert wire and push lever to engage securely.

- Strong spring continuously applies pressure as strands relax
- Eliminates timely step of ferrules
- No torque screwdriver required



[www.hubbell.com/wiringdevice-kellems](http://www.hubbell.com/wiringdevice-kellems)

# Hubbell-PRO

## IEC pin & sleeve devices with NPT threaded back housing



### ORDERING INFORMATION

	Amps	Ratings	NPT Threading	IP67 Connectors	IP67 Plugs*	IP44 Connectors	IP44 Plugs*
Dual Rated	30A	5h 3ØY 347/600 V	1/2"	<b>C530C5WLT12</b>	<b>C530P5WA</b>	<b>C530C5SLT12</b>	<b>C530P5SA</b>
	30A	5h 3ØY 347/600 V	3/4"	<b>C530C5WLT34</b>	<b>C530P5WA</b>	<b>C530C5SLT34</b>	<b>C530P5SA</b>
Dual Rated	30/32A	6h 3Ø 200/346-240/415 AC	1/2"	<b>C530C6WLT12</b>	<b>C530P6WA</b>	<b>C530C6SLT12</b>	<b>C530P6SA</b>
Dual Rated	30/32A	6h 3Ø 200/346-240/415 AC	3/4"	<b>C530C6WLT34</b>	<b>C530P6WA</b>	<b>C530C6SLT34</b>	<b>C530P6SA</b>
Dual Rated	30A	7h 3ØY 277/480 V	1/2"	<b>C530C7WLT12</b>	<b>C530P7WA</b>	<b>C530C7SLT12</b>	<b>C530P7SA</b>
	30A	7h 3ØY 277/480 V	3/4"	<b>C530C7WLT34</b>	<b>C530P7WA</b>	<b>C530C7SLT34</b>	<b>C530P7SA</b>
Dual Rated	30/32A	9h 3ØY 120/208 V	1/2"	<b>C530C9WLT12</b>	<b>C530P9WA</b>	<b>C530C9SLT12</b>	<b>C530P9SA</b>
Dual Rated	30/32A	9h 3ØY 120/208 V	3/4"	<b>C530C9WLT34</b>	<b>C530P9WA</b>	<b>C530C9SLT34</b>	<b>C530P9SA</b>
Dual Rated	60A	4h 125 VAC	3/4"	<b>C360C4WLT34</b>	<b>C360P4WA</b>	<b>C360C4SLT34</b>	<b>C360P4SA</b>
	60/63A	6h 250 VAC	3/4"	<b>C360C6WLT34</b>	<b>C360P6WA</b>	<b>C360C6SLT34</b>	<b>C360P6SA</b>
Dual Rated	60A	7h 480 VAC	3/4"	<b>C360C7WLT34</b>	<b>C360P7WA</b>	<b>C360C7SLT34</b>	<b>C360P7SA</b>
	60A	5h 3ØY 347/600 V	3/4"	<b>C460C5WLT34</b>	<b>C460P5WA</b>	<b>C460C5SLT34</b>	<b>C460P5SA</b>
Dual Rated	60/63A	6h 3Ø 200/346-240/415 AC	3/4"	<b>C460C6WLT34</b>	<b>C460P6WA</b>	<b>C460C6SLT34</b>	<b>C460P6SA</b>
Dual Rated	60A	7h 3Ø 480 V	3/4"	<b>C460C7WLT34</b>	<b>C460P7WA</b>	<b>C460C7SLT34</b>	<b>C460P7SA</b>
	60A	9h 3ØY 120/208 V	3/4"	<b>C460C9WLT34</b>	<b>C460P9WA</b>	<b>C460C9SLT34</b>	<b>C460P9SA</b>
Dual Rated	60A	5h 3ØY 347/600 V	3/4"	<b>C560C5WLT34</b>	<b>C560P5WA</b>	<b>C560C5SLT34</b>	<b>C560P5SA</b>
	60/63A	6h 3Ø 200/346-240/415 AC	3/4"	<b>C560C6WLT34</b>	<b>C560P6WA</b>	<b>C560C6SLT34</b>	<b>C560P6SA</b>
Dual Rated	60A	7h 3ØY 277/480 V	3/4"	<b>C560C7WLT34</b>	<b>C560P7WA</b>	<b>C560C7SLT34</b>	<b>C560P7SA</b>
	60/63A	9h 3ØY 120/208 V	3/4"	<b>C560C9WLT34</b>	<b>C560P9WA</b>	<b>C560C9SLT34</b>	<b>C560P9SA</b>

\*Mating plugs are certified for installation on cable only.



### ACCESSORIES

#### Strain Relief for Liquidtight Conduit

Steel fitting, stainless steel mesh for liquidtight metal conduit and PolyTuff® I non-metallic conduit

#### Straight With Male Fitting

Conduit Trade Size Inches	NPT Fitting Size Inches	Mesh Length		Insulated	Non-insulated
		Inches	(cm)		
1/2	1/2	3.5"	(8.89)	<b>074093512</b>	<b>074093402</b>
3/4	3/4	4"	(10.16)	<b>074093513</b>	<b>074093403</b>



#### Straight Metallic Liquidtight Conduit Fittings

Trade Size (metric designator)	Insulated	Non-Insulated
1/2 (16)	<b>H0501</b>	<b>H050</b>
3/4 (21)	<b>H0751</b>	<b>H075</b>

