

Features

- **Point-to-point, Serverless Audio and One-Way Video**
- **SIP Telephone Access**
- **Card Access Control (RFID or NFC)**
- **Vertical Wide-Angle HD Camera**
- **Surface or Gang Box Mounting**
- **Single Button Operation**
- **Multi-Color Status Indicator**
- **12–24 V dc or PoE / PoE+ Input**
- **Integral 2 W Speaker**
- **One Open-Collector Output**
- **Four Inputs**
- **USB Accessory Connector**



The HUBBCOM™ Remote IP device adds two important features to a HUBBCOM™ system. As a **door** or **gate entry** device it provides the convenience of card entry with the ability to connect to a live attendant for entry. HUBBCOM™ Remote stations give you the option of unlocking an entry via either a Wiegand-compatible security system or a USB-connected remote input/output module. For added peace-of-mind, if an invalid card is tried too many times, a HUBBCOM™ Remote station can go into “lockdown” mode, temporarily disabling the card reader and capturing an image of the person attempting entry.

As a **remote monitoring station**, HUBBCOM™ Remote provides clear video from its HD, ONVIF-compatible camera and audio from a built-in microphone. HUBBCOM™ Remote also gives you the option of making an announcement through the unit’s integral speaker.

In either mode, HUBBCOM™ Remote provides important communications and control functionality and becomes an invaluable part of a HUBBCOM™ IP system.

Specifications

Electrical

Network Power PoE/PoE+, 802.3a f compliant (via RJ45)
 Local Power Requirements 12–24 V dc (a separate, isolated power supply must be provided for each unit)
 Network 10/100/1000 BaseT
 Call Control Signaling (telephone operation) SIP (RF C3261 compliant)

Audio

Integral Speaker 8 Ohm, 2 watt

Mechanical Control

Activation Control Pushbutton with LED ring
 Configurable Inputs (volt-free) 4
 Configurable Outputs 1 open-collector (125 mA max.)

Electronic Output

Status Indication 3-color LED

Mechanical / Environment

Operating Temperature Range -35° C to +66° C; (-31° F to +151° F)
 Relative Humidity up to 95%, non-condensing
 Construction Black PC/PET Plastic
 Dimensions 5.2 W x 6.7 H x 1.6 D inches; (132 W x 171 H x 40 mm)
 Weight 2.0 lbs

Approval Standards

Compliance to Standards FCC CFR 47 Part 15
 CE-Mark

Ordering Information

| Models | Description |
|-----------|---|
| GRC600 | HUBBCOM™ Remote IP Device |
| 12841-001 | External Device Activation Module - EDAM (external USB-connected relay module) |