



Hubbell Industrial Controls, Inc.

4301 Cheyenne Drive
Archdale, NC 27263

Tel: 336-434-2800
Fax: 336-434-2803

Class C Hoist							
Horsepower Rating HD	Amperage	Drive Available torque	Ohms	Watts	Part Number	Ohms	Watts
1	2.1	1027%	80	400	HC57296801	80	400
1.5	3	700%	80	400	HC57296801	80	400
2	3.4	513%	80	400	HC57296802	80	800
3	5.2	350%	80	400	HC57296802	80	800
3	5.2	257%	80	400	HC57296803	80	1200
5	7.6	193%	80	400	HC57296803	80	1200
7.5	11	140%	80	800	HC57296805	80	2000
10	14	205%	40	800	HC57296813	40	2400
15	21	140%	40	1200	HC57296815	40	3600
20	27	211%	20	1600	HC57296826	20	5120
25	34	171%	20	2000	HC57296827	20	6480
30	40	210%	14	3150	HC57296836	14	7400
40	52	154%	14	3600	HC57296837	14	9500
50	65	203%	8	4232	HC57296848	8	12800
60	77	167%	8	5408	HC57296849	8	16200
75	96	202%	6	6144	HC57296857	6	21600
100	124	148%	6	7776	HC57296858	6	29400
125	156	202%	3.5	8750	HC57296864	3.5	35000
150	180	165%	3.5	12600	HC57296864	3.5	35000
175	220	198%	2.5	12960	HC57296873	2.5	45563
200	260	163%	2.5	16000	HC57296874	2.5	49000
300	361	131%	2.5	20250	HC57296875	2.5	56250
350	414	104%	2.5	25000	HC57296876	2.5	72250

CLASS D							
HP ND	Amperage	Drive Available torque	Ohms	Watts	Part number	Ohms	Watts
1	2.1	1027%	80	400	HC57296801	80	400
1.5	3	700%	80	400	HC57296802	80	800
2	3.4	513%	80	400	HC57296802	80	800
3	5.2	350%	80	400	HC57296803	80	1200
3	5.2	257%	80	800	HC57296804	80	1600
5	7.6	193%	80	800	HC57296805	80	2000
7.5	11	140%	80	1200	HC57296807	80	2800
10	14	205%	40	1200	HC57296816	40	4000
15	21	140%	40	2000	HC57296818	40	5600
20	27	211%	20	2400	HC57296828	20	8000
25	34	171%	20	2800	HC57296829	20	10580
30	40	210%	14	3600	HC57296838	14	12000
40	52	154%	14	4500	HC57296840	14	18000
50	65	203%	8	6728	HC57296850	8	20000
60	77	167%	8	6728	HC57296851	8	28800
75	96	202%	6	9600	HC57296858	6	29400
100	124	148%	6	12150	HC57296859	6	43350
125	156	202%	3.5	17150	HC57296865	3.5	50400
150	180	165%	3.5	17150	HC57296866	3.5	68600
175	220	198%	2.5	20250	HC57296876	2.5	72250
200	260	163%	2.5	25000	HC57296877	2.5	81000
300	361	131%	2.5	36000	HC57296878	2.5	100000
350	414	104%	2.5	45563	HC57296879	2.5	162563

CLASS E							
HP ND	Amperage	Drive Available torque	Ohms	Watts	Part number	Ohms	Watts
1	2.1	1027%	80	400	HC57296802	80	800
1.5	3	700%	80	400	HC57296802	80	800
2	3.4	513%	80	400	HC57296803	80	1200
3	5.2	350%	80	800	HC57296804	80	1600
3	5.2	257%	80	800	HC57296805	80	2000
5	7.6	193%	80	1200	HC57296806	80	2400
7.5	11	140%	80	1600	HC57296808	80	3600
10	14	205%	40	2400	HC57296817	40	4800
15	21	140%	40	2800	HC57296819	40	7200
20	27	211%	20	4500	HC57296829	20	10580
25	34	171%	14	5600	HC57296830	20	13520
30	40	210%	14	5600	HC57296839	14	14000
40	52	154%	8	8192	HC57296840	14	18000
50	65	203%	8	10368	HC57296851	8	28800
60	77	167%	8	12800	HC57296851	8	28800
75	96	202%	6	21600	HC57296859	6	43350
100	124	148%	6	21600	HC57296859	6	43350
125	156	202%	3.5	35000	HC57296865	3.5	50400
150	180	165%	3.5	35000	HC57296866	3.5	68600
175	220	198%	2.5	36000	HC57296877	2.5	81000
200	260	163%	2.5	45563	HC57296878	2.5	100000
300	361	131%	2.5	49000	HC57296879	2.5	162563
350	414	104%	2.5	56250	HC57296879	2.5	162563

CLASS F							
HP ND	Amperage	Drive Available torque	Ohms	Watts	Part number	Ohms	Watts
1	2.1	1027%	80	400	HC57296802	80	800
1.5	3	700%	80	400	HC57296803	80	1200
2	3.4	513%	80	800	HC57296804	80	1600
3	5.2	350%	80	800	HC57296805	80	2000
3	5.2	257%	80	1200	HC57296807	80	2800
5	7.6	193%	80	1600	HC57296808	80	3600
7.5	11	140%	80	2000	HC57296809	80	4800
10	14	205%	40	2800	HC57296819	40	7200
15	21	140%	40	4000	HC57296820	40	9600
20	27	211%	20	6480	HC57296830	20	13520
25	34	171%	20	8000	HC57296831	20	16820
30	40	210%	14	9500	HC57296841	14	22000
40	52	154%	14	12000	HC57296842	14	28000
50	65	203%	8	12800	HC57296852	8	39200
60	77	167%	8	16200	HC57296852	8	39200
75	96	202%	6	21600	HC57296860	6	60000
100	124	148%	6	29400	HC57296860	6	60000
125	156	202%	3.5	35000	HC57296867	3.5	101150
150	180	165%	3.5	50400	HC57296867	3.5	101150
175	220	198%	2.5	45563	HC57296879	2.5	162563
200	260	163%	2.5	56250	HC57296879	2.5	162563
300	361	131%	2.5	72250	HC57296880	2.5	225000
350	414	104%	2.5	100000	HC57296880	2.5	225000



A proud member of the Hubbell family

Hubbell Industrial Controls

©2023 Hubbell Industrial Controls. All rights reserved.
 Hubbell, the Hubbell logo are registered trademarks or trademarks of Hubbell Industrial Controls All other trademarks are the property of their respective owners.
hubbell.com/hubbellindustrialcontrols | For quotes: icdorders@hubbell.com