# DG0657

600 Series

Stainless Steel Perforated

PROJECT ID/
CONTRACT NO: _____

LOCATION: _____

**ENGINEERING SPECIFICATION:**

POLYCAST® DG0657 Grate is designed for use where sanitary conditions are essential, as well as the need for heel-resistant grating. Grating locking device Part No. DA0642S (not shown) should be used and maintained secure. The grate has 17% (34in²) of open area. The grate is made 14 gauge GR. 304 Stainless Steel and weighs approximately 8lbs [3.63kg]. The grate is available in both 24" [610mm] and 48" [1219mm] lengths.





DIN APPLICATION LOAD CLASS A:
Residential, pedestrian, cyclist traffic
Designed for a distributed pressure of 3,372 lbs (15 kN).

Meets the following Standards & Specifications:

- DIN 19580 / DIN EN 1433 Drainage Channels for Vehicular and Pedestrian Areas
- The Americans with Disabilities Act of 1990: 4.5.4
- ASME A112.6.3: Section 7.12 Heel Resistant Strainers and Grates
- Australian Standard AS 3996-2006 Clause 3.3.6