

Newest Addition to the Versa-Tech® Recloser Family

VERSA-TECH® LT

Single Phase Recloser

FOR 100A CONTINUOUS
CURRENT APPLICATIONS

FEATURES

- For use on lines up to 100 Amp continuous
- Rated at 29.3 kV, 4kA Interrupting
- Wirelessly programmable with WiFi or Digi radios
- Simple functionality



RATINGS AND SPECIFICATIONS

Rated Maximum Voltage.....	29.3kV
Rated Continuous Current.....	100A
Fault Make Capacity.....	4kA
Fault Break Capacity.....	4kA
Mechanical Operations.....	10,000
3 Second Withstand Current.....	4kA
Transformer Magnetizing Current.....	14A
Cable Charging Current.....	25A
Line Charging Current.....	5A
Lightning Impulse Withstand.....	125kV
60Hz, 1-Minute Withstand Voltage.....	60kV
Maximum Terminal Pad Load kg (pounds).....	4 (30)
Operating Temperature.....	-40C to 60C
Weight kg (pounds).....	21 (46)