

Crimp Tool

Dual hex cavity: 0.178"/0.151", flat crimp 0.052", hex crimp 0.136", hardened die

Catalog No. Description For SC/ST-style epoxy/ OFCMT04 anaerobic or crimp style connectors



Fiber Strip Tools

Description	Catalog No.
Universal 250/900 μ , 2.0,	OFSTRIP2



Kevlar® Cable Scissors

Description	Catalog No.
or cutting Kevlar® einforced cables up to	OFSCSRS
4-strand, non-armored	

Kevlar is a registered trademark of E.I. du Pont de Nemours and Co.



Fiber Cleavers

Description	Catalog No.
Multimode fiber only	OFCLV3
SM or MM fiber, precision, with case	OFCLV5

Field Termination Kit



Termination Kit for SC/ST Style Connectors

Includes:

- Heat-cure epoxy oven (110V)
- Tool pouch (OFTP02C)
- Fiber preparation tool
- Cable preparation tool
- Heat cure epoxy
- Anaerobic adhesive
- Anaerobic primer • Polishing paper

Description Catalog No.	Field epoxy termination kit	OFTK03C
	Description	Catalog No.

Cleaning Sticks



Sticklers® CleanStixx™, SC/ST/FC/APC

Includes: (1) 50 pack disposable cleaning sticks

Catalog No. Description SC/FC/APC 2.50mm **OFSTIX50SC** port cleaning sticks



Sticklers® CleanStixx™, LC/MU/APC

Includes: (1) 50 pack disposable cleaning sticks Catalog No.

LC/MU/APC 1.25mm **OFSTIX50LC** port cleaning sticks

Cleaning Wipes



Sticklers® CleanWipes™, Dispenser

Includes: (1) roll of 90 sheets Catalog No. Description Tube of 90 lint-free **OFWIPES90** sheets, multi-purpose



Sticklers® CleanWipes™, **Cartridge**

Includes: (1) 4-slot box

Description Catalog No. **OFWIPES400** Box of 100 lint-free sheets, 4 wipes/sheet

Scribing



Hand Scribe Tool

Includes: (1) tool and scribe guide Description Catalog No. **OFSCRIBE** Sapphire blade



Scribe Guide Fixture

6-pack	
Description	Catalog No.
Suitable for SC, ST-style, or LC connectors	OFSG

STRIPPING

Use a precision strip tool sized correctly to remove 900µm or 250µm buffer coatings, and cable jackets up to

- Strip buffer coatings in small increments with a firm, steady motion to avoid breaking fiber.
- The tool should not break the glass fiber.
- Gently bend the fiber to check for nicks. A nicked fiber will break easily.
- Clean the fiber with a wipe and cleaning fluid.

Cable clips

Description



CLEAVING

A precision cleaved fiber has a flat end with zero cleave angle and no cracks, pits or edge fractures.

- Use a precision cleave tool for terminating prepolished mechanical splice connectors, which are sensitive to cleave quality.
- For adhesive connectors, use a scribe fixture to control cleaved fiber height for best polishing results.
- Cleaved separation is achieved by scoring and applying tension to the fiber. Bending causes high cleave angle and fractures.



INSPECTING

Always "clean and inspect before you connect" using Hubbell cleaning products and a 200x or 400x microscope.

• The polished fiber end face must be free of contamination, residue, cracks, chips or scratches.

• Polishing pad

• Safety glasses

Cure adapters

Wipes

Syringes


Needles

Clips

• Canned air 10oz

- Clean connector tips using Hubbell lint-free wipes and optical grade fiber cleaning fluid.
- Clean fiber ports using 1.25mm cleaning sticks for LC ports and 2.5mm sticks for SC ports.





Proactive cleaning before you

connect keeps contamination out o

- Avoid contamination failures and subsequent re-testing.
- Eliminate cross-contamination from dirty
- Optimize network performance.
- Protect investment in fiber infrastructure.



Cleaning Kit 1 without Sticklers® CleanClickers®

Cleaning Kits

Description Catalog No. Cleaning kit without **OFCLEANKT1**



Cleaning Kit 2 with Sticklers® CleanClickers®

Catalog No. Cleaning kit with LC, **OFCLEANKT2** SC, MPÖ clickers

Sticklers, CleanClicker, CleanStixx and CleanWipes are trademarks of MicroCare.

Includes: (1) disposable cleaner tape cartridge

2.5mm, LC/MU/APC **OFCLICK750LC**

Catalog No.

Sticklers® CleanClicker®,

LC/MU/APC

Description

Cable Management



Fiber Management Spool

Adhesive mount, yellow	OFSPOOLPK2
Description	Catalog No.
2-pack	



Catalog No.
CCPS1
CCPS2
CCPS3



Fiber Cable Management Radius Clips

Includes: pack of (4) self-adhering clips with bend radius control element Catalog No. Description

FBRMGTCLPK4

Catalog No.



Loose Tube OSP Cable Break-Out Kits

ncludes: tube kit, break-out block and crimp bushing

<u> </u>	
6-fiber break-out kit	OFBOKT6
12-fiber break-out kit	OFBOKT12

Adhesive Kits



Epoxy Adhesive Kit Includes: (6) tubes 1g, (6) syringes/needles

escription	Catalog No.
asy mix 1g tubes	OFCEP



Angerobic Adhesive Kit

Includes: Primer and adhesive, (10) syringes and (10) needles Catalog No. Description

Anaerobic adhesive kit cures in 6–10 seconds	OFCAP
Replacement bottle of primer only	OFPRIME

Fusion Splice



Fusion Splice Sleeves 25-pack

Description Catalog No. FSHST401025 40mm length, 10mm cleave 12-fiber ribbon FRSHST401025



Fusion Splice Trays

Description	Catalog No.
Aluminum, 12-fiber	STRAY12F
Aluminum, 24-fiber	STRAY24F
Plastic, yellow, 24-fiber	OFSPLKT24F

Cleaning Accessories



Sticklers® CleanClicker®, SC/ST/FC/APC

Includes: (1) disposable cleaner tape cartridge Catalog No. Description 2.5mm, SC/FC/APC **OFCLICK750SC**



Sticklers® CleanClicker®, MPO/APC

Includes: (1) disposable cleaner tape cartridge Catalog No. Description MPO male, female, OFCLICK600MPO flat/APC



Sticklers® Cleaning Fluid, Optical

Includes: (1) 3oz pump dispenser Catalog No. Description OFCLEANER3OZ 3oz cleaning fluid, pump, non-hazardous



www.hubbell-premise.com www.hubbell-premise.com www.hubbell-premise.com

Installation Kits



Connector Installation Tool Kit

udes: sapphire scribe, scribe guide, black permanent marker, carbon fiber scissors, strip emplate and polishing fixture, ruler, buffer/ cable jacket stripper, 200X microscope assembly, crimp tool and die

Description	Catalog No.
For SC/ST-style	OFTP02C
connectors crimp or	
adhesive termination	



Epoxy Cure Adapters

cludes: package of (6) adapters for heat

Description	Catalog No.
SC/ST-style	OFCA
LC	OFCALC



TESTING

The fiber link total dB loss is measured through the mated connector pair on each end using an insertion loss test set.

- Testers should be calibrated, and fiber ports cleaned and inspected prior to use.
- Clean and inspect test jumpers prior to mating into tester and fiber link ports.
- A 2-connector fiber link insertion loss should be less than 1.5dB, excluding cable loss.



Epoxy and Crimp Kit

Includes: OFSTRIP2 and OFCMT04 tools, polishing pucks, 200X microscope, carbon fiber scissors, scribe, glasses, alcohol wipes

Field install kit	OFTK05
Description	Catalog No.



LC Duplex Connector Extraction Tool

ncludes: (1) tool, individually packaged, ideal for servicing high density interconnections

Connector extraction tool	OFLCDTOOL1
Description	Catalog No.





Polishing Fixture

Includes: (1) stainless steel puck, polished surface; SC/ST-style or LC compatible

.C	OFPUCKLC
SC/ST-style	OFPUCK
Description	Catalog No.



Polishing Film

Includes: (25) each of 5μ , 1μ and 0.3μ sheets,) polishing pad

Replacement kit	OFLFP
Description	Catalog No.
71 01	

Inspecting



9	ST, SC, LC microscope	OFSCOPE2
P	Description	Catalog No.
D	Includes: batteries, LC adapter, soft pouch	
		(0., 00, =0)





	Includes: batteries, LC adapter, holster, wrist strap, end protectors	
	Description	Catalog No.
	Visual fault locator	OFVFLKT1
	LC adapter, separate	OFVLCADP
	TIP: Use a VFL during termination for optimum	



Microscope, 400X

Includes: built-in illuminator, batteries,

3C/31 style adapter, son poor	-11
Description	Catalog No.
SC/ST-style microscope	OFSCOPE1
LC adapter (400X microscope only)	FOADPTLC




Multimode Test Set

Includes: (1) power meter, (1) dual wavelength LED source, (1) soft pouch, batteries

Description	Catalog No.
Complete tester kit	OFPLK813A
Power meter dual wavelength	OFPM813
LED light source dual wavelength, multimode	OFLS813

nClicker





[your complete online resource]

Find what you need quickly with our multi-functional online value-added tools print, zoom, search and download required information anytime, anywhere.

[related literature]



HUBBELL®
Premise Wiring

Fiber Optics Tooling & Maintenance Product Guide



FIBERSURE

FIBERSURE

STICKLER

NET 1 FL OZ. (29.57 # ADHESIVE

FIBER OPTIC PRIMER



Hubbell Premise Wiring • Hubbell Incorporated (Delaware) • 23 Clara Drive • Suite 103 • Mystic, CT 06355 • Phone (800) 626-0005 • FAX (860) 535-8328



