

Fiber Wall Mount Enclosures

Our line of Wall Mount fiber distribution units are designed to support patching and splicing in one unit. The enclosures have panel positions, allowing for a wide variety of fiber termination connector types, including splice cassettes, fiber adapter panels and LGX compatible adapter plates.

Two compartments separate the network terminations from the distribution terminations.

All Products are TAA/GSA Compliant

FCW Series Double Door Enclosures



FCW4SPT

- Accommodates up to 48 Fiber Ports
- Suitable for loose tube, tight buffer and ribbon cable
- Cable entry tie down points
- Double door with key lock
- Top or bottom cable entry



FCW12SPT

- Accommodates up to 144 Fiber Ports
- Suitable for loose tube, tight buffer and ribbon cable
- Cable entry tie down points
- Double door with key lock
- Top or bottom cable entry
- LGX compatible adapter plates

The four-panel FCW4SPTRD is safety red for your Public Safety Equipment Room.

FCW4SPTRD

- Accommodates up to 48 Fiber Ports
- Suitable for loose tube, tight buffer and ribbon cable
- Cable entry tie down points
- Double door with key lock
- Top or bottom cable entry
- LGX compatible adapter plates



FTU Series Single Door Enclosures with Optional Door Lock



FTU4SPT

- Accommodates up to 48 fiber ports
- Suitable for loose tube, tight buffer and ribbon cable
- Cable entry tie down points
- Top or bottom cable entry
- Accepts 4 LGX compatible adapter plate



Front Door Open



Rear Door Open

FTU2SPH

- Partitioned access: building/end user
- Accepts (2) FSP panels
- Holds (3) 7" splice stays (STRAY12F)
- Lightweight aluminum construction



FTU2SPT

- Accommodates up to 24 fiber ports in 2 LGX adapter plate slots
- Suitable for loose tube, tight buffer and ribbon cable
- Cable entry tie down points
- Top or bottom cable entry



FTU1SPT

Dual Hinge Enclosure

- Accommodates up to 12 fiber ports
- Suitable for loose tube, tight buffer and ribbon cable
- Cable entry tie down points
- Accepts one LGX compatible adapter plate

FCW Series Wall Mounts

Height (in)	Width (in)	Depth (in)	Color	Weight (lb)	FS Panel Capacity	Splice Tray Capacity	Splice Cassette Capacity	Catalog No.
15	15	6	Black	15	12	8	12	FCW12SPT
11	15	3.5	Black	7	4	4	4	FCW4SPT
11	15	3.5	Red	7	4	4	4	FCW4SPTRD

FTU Series Wall Mounts

All Products are TAA/GSA Compliant

Height (in)	Width (in)	Depth (in)	Color	Weight (lb)	FS Panel Capacity	Splice Tray Capacity	Splice Cassette Capacity	Catalog No.
5.5	6.25	6.3	Black	5	1	12 position splice chip	0	FTU1SPT
9.5	13	3.5	Black	7	2	4	2	FTU2SPT
11.5	13	3.5	Black	8	4	4	3	FTU4SPT
8.2	13	5	Black	5	2	3	0	FTU2SPH

Optional Locking Kits

Description	Catalog No.
Lock Kit for cabinets keyed the same as FCWT Technician side	FLOCK3
Lock Kit for cabinets keyed differently than the FCWT Technician side	FLOCK4