



# LINEAR HIGH BAY

## PRODUCT SELECTION GUIDE

|  |  | GOOD  |  | BEST  |     |
|--|--|---|--|---|-----|
|  |  | tradeSELECT <sup>®</sup>  |  | High-Spec Linear High Bay   |     |
|  |  |  |  |  |     |
|  |  | CLB   |  | PEL   |     |
| FEATURES                                 | Length                                     | 2'  | 4'   | 2'  | 4'  |
|  |  | Yes   | Yes  | Yes   | Yes |
|  | Mounting Height                            | Up to 60'   |  | Up to 60'   |     |
|  | Lumens (maximum)                           | 10,000- 57,000  |  | 8000–60,000   |     |
|  | Efficacy (maximum LPW)                     | 137–158   |  | 146–177   |     |
|  | CRI  | 80  |  | 80+   |     |
|  | CCT  | 4000K, 5000K  |  | 3000K, 3500K, 4000K, 5000K  |     |
|  | Wattage                                    | 75–388W   |  | 50–410W   |     |
|  | Voltage                                    | 120–277, 347–480*   |  | 120–277V, 347V, 480V  |     |
|  | Distribution                               | Wide, Narrow*   |  | Narrow, Wide, Lambertian  |     |
|  | Lens                                       | Polycarbonate   |  | No Lens, Acrylic, Polycarbonate   |     |
|  | Uplight                                    | No  |  | Yes   |     |
|  | Temperature Range                          | -40° to 50° C   |  | -40°C to 65°C   |     |
|  | Dimming                                    | 0-10V Dimming to 10%  |  | 0–10V Dimming to 5%   |     |
|  | Ratings                                    | Damp Location, IP4X, IK10 Impact  |  | Damp Location   |     |
|  | Emergency Battery Pack                     | 15W*  |  | 10W, 20W  |     |
| Equivalency                              | 100W to 1000W HID & 4–lamp T8, 8–lamp T5HO |   | 100W to 1000W HID & 4–lamp T8, 8–lamp T5HO |   |     |
| DLC <sup>®</sup> DesignLights Consortium | Yes  |   | Yes  |   |     |
| Buy America(n) Solutions                 | –  |   | TAA FAR §52.225-11                         |   |     |
| INTEGRATED CONTROLS                      | Standalone Occupancy & Daylighting         | Yes*  |  | Yes   |     |
|  | NX Standalone Occupancy & Daylighting      | –   |  | Yes   |     |
|  | NX Networked Occupancy & Daylighting       | –   |  | Yes   |     |
|  | PowerHUBB <sup>™</sup>                     | –   |  | –   |     |
| USES                                     | Applications                               | Industrial, Gymnasium, Warehouse, Big Box Retail                                  |  | Industrial, Gymnasium, Warehouse, Big Box Retail                                    |     |

DLC<sup>®</sup> (DesignLights Consortium) Qualified. Please refer to the DLC website for specific product qualifications at [www.designlights.org](http://www.designlights.org)