




# ROUND HIGH BAY

## PRODUCT SELECTION GUIDE

		GOOD		BETTER
		tradeSELECT <sup>®</sup>  CRB		tradeSELECT <sup>®</sup>  CRN2
				Mid-Spec Round High Bay  UTB2
FEATURES	Diameter	11.75"	14.13"	14.56"
	Mounting Height	Up to 40'		Up to 40'
	Lumens (maximum)	14,000–34,000		14,000–36,000
	Efficacy (maximum LPW)	139–143		124–144
	CRI	80		80+
	CCT	4000K, 5000K		4000K, 5000K
	Wattage	100–240W		84–190W
	Voltage	120–277V		120–277V; 347–480V
	Distribution	–		Reflector: Clear, Diffuse, Aluminum
	Lens	Glass, Frosted Polycarbonate		Conical Drop Lens Dropped Lens Refractor, Frosted Acrylic Lens, None
	Temperature Range	-30°C to 50°C		-40°C to 55°C
	Dimming	0–10V Dimming to 10%		0–10V Dimming to 10%
	Ratings	Wet Location, IP66, IK07 Impact		Damp Location
	INTEGRATED CONTROLS	Emergency Battery Pack	25W Field Installable	
Equivalency		250W to 750W HID		175W to 750W HID
DLC <sup>®</sup> DesignLights Consortium		Yes		Yes
Standalone Occupancy & Daylighting		–		Yes
USES	NX Standalone Occupancy & Daylighting	–		Yes
	NX Networked Occupancy & Daylighting	–		Yes
	PowerHUBB <sup>™</sup>	–		–
Applications	Industrial, Gymnasium, Warehouse, Big Box Retail, Garden Center		Industrial, Gymnasium, Warehouse, Big Box Retail	

DLC<sup>®</sup> (DesignLights Consortium) Qualified. Please refer to the DLC website for specific product qualifications at [www.designlights.org](http://www.designlights.org)