





# STRIPS

## PRODUCT SELECTION GUIDE

		GOOD			BETTER						BEST		
		tradeSELECT <sup>®</sup>			Mid-Spec Strip			Mid-Spec Strip			High-Spec Strip		
													
		CSL			LCS			LCL			MPS		
FEATURES	Length	2'	4'	8'	2'	4'	8'	2'	4'	8'	2'	4'	8'
		–	Yes	Yes	Yes	Yes	Yes	Yes	Yes	Yes	Yes	Yes	Yes
	Continuous Row	–			–			–			Yes		
	Lumens (maximum)	9959			23,274			21,354			17,490		
	Efficacy (maximum LPW)	142			153			144			148		
	Lens	Frosted Acrylic			None			Frosted Acrylic			None, Frosted Acrylic, Polycarbonate		
	Emergency Battery Pack	–			Yes			Yes			Yes		
	CRI	80+			80+			80+			80+/90		
	SpectraSAFE™	–			–			–			Yes		
	Switchable Technology	Switchable Lumen & CCT			–			–			–		
	SpectraSync™ Color Tuning Technology	–			–			–			Yes		
	DLC® DesignLights Consortium	Standard			Premium			Premium			Premium		
	Buy America(n) Solutions	–			–			TAA FAR §52.225-11			TAA FAR §52.225-11		
INTEGRATED CONTROLS	Standalone Occupancy & Daylighting	–			–			–			Yes		
	NX Standalone Occupancy & Daylighting	–			–			–			Yes		
	NX Networked Occupancy & Daylighting	–			–			–			Yes		
	PowerHUBB™	–			–			–			Yes		
USES	Applications	Education, Healthcare, Office, Retail, Industrial			Education, Healthcare, Office, Retail, Industrial Yes			Education, Healthcare, Office, Retail, Industrial			Education, Healthcare, Office, Retail, Industrial		

DLC® (DesignLights Consortium) Qualified. Please refer to the DLC website for specific product qualifications at [www.designlights.org](http://www.designlights.org)