






PANELS & TROFFERS

PRODUCT SELECTION GUIDE

		GOOD			BETTER			BEST		
		tradeSELECT   CBT Back-Lit Troffer			tradeSELECT   CFP Edge-Lit Flat Panel			High-Spec Panel  Scaler™ Edge-Lit Flat Panel		
FEATURES	Sizes	1x4	2x2	2x4	1x4	2x2	2x4	1x4	2x2	2x4
		Yes	Yes	Yes	Yes	Yes	Yes	Yes	Yes	Yes
	CRI	80+			80+			80+		
	CCT	3500K, 4000K			3500K, 4000K			3000K, 3500K, 4000K, 5000K		
	SpectraSync™ Color Tuning Technology	-			-			3000-5000K		
	Switchable Technology	Switchable Lumen, CCT			Switchable Lumen & CCT			-		
	SpectraSAFE™ Integrated Surveillance	-			-			-		
	Lumen Range	3044-6211			2876-7534			1492-8995		
	Mounting	Recessed	Surface	Cable	Recessed	Surface	Cable	Recessed	Surface	Cable
		Yes	Yes	-	Yes	Yes	Yes	Yes	Yes	Yes
	Dimming	1-10V Dimming to 10%			0-10V Dimming to 10%			0-10V Dimming to 1% and Dim to Dark		
	Emergency Battery Pack	-			Yes			Yes		
	DTS (UL924 Bypass)	-			-			Yes		
	Flex	-			Yes			Yes		
Efficacy (maximum LPW)	136			137			145			
DLC® DesignLights Consortium	Standard			Premium			Standard & Premium			
INTEGRATED CONTROLS	Standalone Occupancy & Daylighting	-			-			-		
	NX Standalone Occupancy & Daylighting	-			-			-		
	NX Networked Occupancy & Daylighting	-			-			-		
	PowerHUBB™	-			-			-		
USES	Applications	Education, Healthcare, Office, Retail			Education, Healthcare, Office, Retail, Cleanroom (ISO Class 5-9 Rating)			Education, Healthcare, Office, Retail, Cleanroom (ISO Class 5-9 Rating)		

DLC® (DesignLights Consortium) Qualified. Please refer to the DLC website for specific product qualifications at www.designlights.org