

HDPJ High Density Jack Panels

Double your port density for maximum flexibility

Provide more connectivity anywhere space is at a premium. Hubbell high density jack panels feature a flexible, modular 1/2 rack unit design with 24 ports. It doubles the ports available in the space of a standard panel while offering better service access.


The unloaded panel design delivers efficient rack and cabinet utilization and custom port density solutions. Mix categories, colors, services, and media at the panel level. It allows the port count to grow with your network demands. Stack multiple panels to create 48, 72, or 96 port solutions.

These panels include rear cable management bars. This provides enhanced strain relief and ANEXT management, along with one part number ordering simplicity. The front face features space for standard 1/4" adhesive label tape.

- 24 ports in a 1/2 rack unit height
- Terminate jacks and snap into place for increased efficiency and greater flexibility
- Cable management bar included

Three models

Choose standard flat, shielded, or angled versions. The angled option saves even more space by eliminating the need for horizontal cable management.



- Quarter inch label tape compatible
- Cold rolled steel construction for superior strength
- Ideal for Category 6A installations



HDPJ High Density Jack Panels

Designed for maximum flexibility and expansion.



Part Numbers & Ordering Information

HDPJ Multimedia Jack Panels, Unloaded

Type	Color	Width Inches (mm)	Height Inches (mm)	Ports	Rack Units	Catalog No.
Flat	Black	19" (483)	0.875" (23)	24	1/2	HDPJ24
Angled	Black	19" (483)	0.875" (23)	24	1/2	HDPJ24A¹
Flat, Shielded	Silver	19" (483)	0.875" (23)	24	1/2	HDPJS24

¹HDPJ24A angled panel protrudes 4.2" from the plane of the rack.



HJU6AGY



HJS6A



HJU6Y



**Category 6 Jack
HXJ6GN**



**Category 5e Jack
HXJ5EB**



**USOC Jack
HXJUEI**

NEXTSPEED® Ascent and Xcelerator Jacks

Termination Style	Unit of Measure	Category					
		6A	6A Shielded	6	6 Shielded	5e	USOC Jack
Cobra-Lock	Single pack	HJU6Axx	HJS6A**	HJU6	HJS6**	—	—
Cobra-Lock	24 pack	HJU6Axx24	HJS6A24**	HJU624	HJS624**	—	—
Punch-down	Single pack	—	—	HXJ6xx	—	HXJ5Exx	HXJUxx
Punch-down	24 pack	—	—	HXJ6xx24	—	HXJ5Exx24	—

xx = Color: **BK** (Black), **B** (Blue), **EI** (Electric Ivory), **GL** (Gold*), **GY** (Gray), **GN** (Green), **OW** (Office White), **OR** (Orange), **P** (Purple), **R** (Red), **W** (White) or **Y** (Yellow).

PK (Pink), **BN** (Brown) for **HJU** and **HJS** series only.

*Gold and Purple available in 24-pack only.

**Note: HDPJ Panels are compatible with HJS6A and HJS6 jacks without color face inserts.

HDPJ series panels are not compatible with HJS6Axx and HJS6xx series jacks with colored face inserts installed. Remove colored face before installing jack into panel.