

SOCKET STYLE ROCK ANCHOR

NEW STYLE ROCK ANCHOR FOR GUYING APPLICATIONS



FEATURES AND BENEFITS

- Socket makes 360 degrees of contact with rock
- Socket will tighten as load increases
- Spin socket by hand to adjust to hole size before installation
- After anchor is installed, finish tightening by applying torque through rod
- Max tension rating
 - ¾" rod = 23,000 lbs
 - 1" rod = 36,000 lbs
- Steel rod and ductile iron socket
- Galvanized per ASTM A-153

HUBBELL SKU	Rod Diameter	Rod Length	Hole Size Required
R315H	¾"	15"	2"
R330H	¾"	30"	2"
R353H	¾"	53"	2"
R360H	¾"	60"	2"
R372H	¾"	72"	2"
R384H	¾"	84"	2"
R396H	¾"	96"	2"
R130LH	1"	30"	2.5"
R153LH	1"	53"	2.5"
R172LH	1"	72"	2.5"
R196LH	1"	96"	2.5"

