

MULTI-RANGE VOLTAGE INDICATOR (MRVI)

WITH BLUETOOTH® CONNECTIVITY FOR DISPLAY ON MOBILE DEVICE


Chance® Lineman Grade Tools™ introduces the Multi-Range Voltage Indicator (MRVI), used to determine if power lines are at rated voltage, have induced voltage or are de-energized. Must be used with properly selected universal hot stick, even with rubber gloves.

FEATURES & BENEFITS

- Visible voltage indicator with range from Capacitive Test Point up to 80kV Phase-to-Phase
- Bluetooth connectivity to view MRVI display live on a mobile device
- Large, easy-to-read dial face and brightly illuminated pointer indicate the voltage class.
- The class displayed is the approximate phase-to-phase and phase-to-ground voltage classes
- Can be used on overhead and underground lines with proper adapters
- Equipped with hold feature
- Battery Drawer for easy battery replacement with Lithium or Alkaline AA batteries
- Comes with storage bag designed to attach to line worker's belt
- Lightweight, 1.25 lbs versus the 2.5 lbs. of the MRVD, C4030979

OPTIONAL FIELD TESTER

- The Multi-Range Voltage Indicator can be field tested with the Voltage Indicator Tester PSC4033582



Mobile App Display

PART NUMBER

PSC4033710

DESCRIPTION

Multi-Range Voltage Indicator

WEIGHT

1-1/4 lbs.

The *Bluetooth*® word mark and logos are registered trademarks owned by Bluetooth SIG, Inc. and any use of such marks by Hubbell Power Systems, Inc. is under license. Other trademarks and trade names are those of their respective owners.



CHANCE Lineman Grade Tools | Hubbell Power Systems, Inc. | hubbellpowersystems.com

©Copyright 2016 Hubbell Incorporated. Because Hubbell has a policy of continuous product improvement, we reserve the right to change design and specifications without notice.

