

SHORT CIRCUIT STICK

NEW GROUNDING TOOL

CHANCE® Lineman Grade Tools™ introduces the Short Circuit Stick with spring loaded clamps for bare vertical secondary overhead systems.

FEATURES

- Rated and tested per IEC 61230 at 3kA/1 Second
- Handle meets ASTM F711 and IEC 60855
- Clamps are connected by an aluminum channel mounted on a 27 mm diameter Epoxiglas® pole
- Clamps are spring loaded and allow connection of the phases to the neutral in one swift movement
- Available with 4 clamps, 5 clamps, or as a dual unit with 4 and 5 clamps, and clamp spacing options of 20 cm or 30 cm
- Conductor range: Min. 3.5 mm up to Max. 19.5 mm diameter



PART NUMBER	DESCRIPTION	CLAMP SPACING	WEIGHT
PST6003583	Short Circuit Stick w/ 4 clamps	20 cm	1.2 kg
PST6003584	Short Circuit Stick w/ 5 clamps	20 cm	1.5 kg
PST6003585	Short Circuit Stick w/ 4 and 5 clamps	20 cm and 20 cm	2.1 kg
PST6003615	Short Circuit Stick w/ 4 clamps	30 cm	1.3 kg
PST6003616	Short Circuit Stick w/ 4 and 5 clamps	30 cm and 20 cm	2.2 kg



CHANCE Lineman Grade Tools | Hubbell Power Systems, Inc. | hubbellpowersystems.com

©Copyright 2019 Hubbell Incorporated. Because Hubbell has a policy of continuous product improvement, we reserve the right to change design and specifications without notice.

