

























HUBBELL RESIDENTIAL

WIRING DEVICE CATALOG

WELCOME TO HUBBELL RESIDENTIAL

Hubbell offers a complete line of high-performance wiring products designed to meet the needs of homebuilders, architects and designers alike. Our residential devices and advanced communication products are built with all the innovation and advantages you've come to expect from Hubbell.

WHY HUBBELL?

We are a company committed to redefining the devices that provide the essentials of power, voice and data in the home.

SERVING YOU EFFICIENTLY

Hubbell is committed to being your single quality source for residential wiring devices for years to come. As always, innovation goes far beyond our products. You now get the most complete residential, commercial and industrial product offering in the industry from one source. You can enjoy all the benefits of reduced transaction costs and improved fulfillment accuracy with our leading electronic ordering, inventory tracking and invoicing systems.

OUR COMMITMENT TO EXCELLENCE

Hubbell continues to provide you with the products and product features you desire - all designed, built and delivered with the quality you have come to expect.

The quality you expect from a name you can trust.

TABLE OF CONTENTS

	_		
IDEVICES®	4	POWER	
STANDARD &		DELIVERY SYSTEMS	16
DECORATOR SWITCHES	6	STRUCTURED WIRING	18
LIGHTING CONTROLS	8	ENTERTAINMENT	
TAMPER-RESISTANT		SYSTEMS	20
RECEPTACLES	10	VOICE/DATA	
SPECIALTY RECEPTACLES	11	CONNECTIONS	21
GFCI/AFCI RECEPTACLES	12	WALLPLATES	22
SURGE PROTECTION	13	OUTDOOR SOLUTIONS	24
CHARGING SOLUTIONS	14	ELECTRIC VEHICLE CHARGING STATION	26



Add comfort, connectivity, and accessibility to any living space.



\$iDevices

Make the Everyday Extraordinary

A truly smart home does more than connect homeowners — it works for them. With iDevices' advanced smart home products, homeowners experience an unparalleled level of comfort, convenience, and security every day. iDevices products give homeowners the power to control their entire living space with the iDevices Connected app, or their voice using Siri®, Amazon Alexa, and the Google Assistant.

- · WiFi & Bluetooth enabled
- Guided in-app setup
- Control through the Connected app or voice control with Siri, Amazon Alexa or the Google Assistant
- · iDevices connect to home Wi-Fi networks; no separate hub required









EVERYTHING YOU LOVE ABOUT YOUR HOME, IN ONE APP®















iDevices® Smart Home Products

Description	Rating	Catalog Number
Wall Switch Multi-way enabled, single pole, 3- and 4-way setup operation, white	Input/output: 15A 120V AC, 6.5A 277V AC, 50/60Hz, 1HP @ 120 & 277V AC	IDEV0008HW
Dimmer Switch Multi-way enabled, CFL/LED, supports forward-phase dimming, single pole, 3- and 4-way setup operation, white	Input/output: 15A 120V AC, 60Hz, 400W Incandescent/halogen, 150W CFL/LED	IDEV0009HW
Wall Outlet 15 amp tamper-resistant receptacle, individual control of each outlet with energy monitoring on both outlets, white	Input/output: 15A 125V AC, 60Hz,1/2 HP	IDEV0010HW
Instant Switch Wireless transmitter, takes 1 CR2032 coin cell battery, wallplate included, white	3V DC, 5.4mA	IDEV0020
Instinct™ Switch With Built-In Alexa, features premium SOEN® Audio technology, speaker and microphone, wallplate included, white	Input/output: 120V AC, 60Hz, 150W CFL/LED, 600W Incandescent, 1000 Resistive, ½HP @ 120V AC	IDEV0022
Thermostat Heating/cooling: 1 and 2 stages, heat pump: 1 and 2 stage with aux or emergency heat, fan control, converts to Fahrenheit or Celsius, white	24V systems	IDEV0005AND5
Universal Thermostat Wire Adapter Share two signals over one wire to add a C/Common wire to a system	18 to 30VAC, 50Hz or 60Hz, 5A Terminals: RC, RH, Y, W, C, G	IDEV0011

^{© 2020} iDevices, LLC. All Rights Reserved. iDevices and Sweetblue are trademarks owned by iDevices, LLC. Apple, the Apple logo, iPad, iPhone, and iPod Touch are trademarks of Apple Inc., registered in the U.S. and other countries. App Store is a service mark of Apple Inc. The Bluetooth* word mark and logos are registered trademarks owned by Bluetooth SIG, Inc. and any use of such marks by iDevices, LLC is under license.











Z-Wave

Alongside the WiFi based iDevices line we offer a broad range of Z-Wave smart products that offer convenience and more integrations—like Alarm.com, ADT, Ring, and vivint—at a lower cost. Z-Wave is a different wireless system that creates a mesh network between your products to enhance communications and uses a hub to then communicate back to your home WiFi. With these products you can diversify your smart home with dimmers, switches, receptacles, sensors, and plugs.

- Wirelessly control and schedule your smart home products
- · All products Z-wave Plus certified
- Control through partner app and enable voice control with Amazon Alexa or the Google Assistant
- Connect to home Wifi networks through partner hub









Z-Wave Smart Home Products

2 Wave Gillart Hollie Froducts		
Description	Rating	Catalog Number
Z-Wave Smart Switch Multi-way enabled, single pole, 150ft range, decorator, white	Input/output: 15A 120V AC, 1800W resistive, 960W incandescent, 1/2 HP	IDEVZ01DW
Z-Wave Smart Dimmer Input/output: 120V AC, 60Hz, Multi-way enabled, CFL/LED, universal dimming, single pole, 150ft range, decorator, white 300W CFL/LED		IDEVZ05DW
Z-Wave Add-on Switch 3- and 4-way add-on switch or dimmer, 150ft range, decorator, white Input/output: 15A 120V AC, 60Hz,1.		IDEVZ03DW
Z-Wave Smart Receptacle 15A tamper-resistant receptacle, one smart controllable outlet, 150ft range	Input/output: 15A 120V AC, 60Hz,1/2 HP	IDEVZ08W
Z-Wave Smart Fan Switch Adjusts fan speeds, light control separately, 150ft range, white	Input/output: 120V AC, 60Hz,1/2 HP	IDEVZ07W
Z-Wave Smart Toggle Switch Multi-way enabled, single pole, 150ft range, toggle, white	Input/output: 15A 120V AC, 1800W resistive, 960W incandescent, 1/2 HP	IDEVZ01TW
Z-Wave Smart Toggle Dimmer Multi-way enabled, CFL/LED, universal dimming, single pole, 150ft range, toggle, white	Input/output: 120V AC, 60Hz, 400W-600W incandescent/halogen, 300W CFL/LED	IDEVZ05TW
Z-Wave Add-on Toggle Switch 3- and 4-way add-on switch or dimmer, 150ft range, toggle, white	Input/output: 15A 120V AC, 60Hz,1/2 HP	IDEVZ03TW





DECORATOR & STANDARD SWITCHES

StyleLine® Decorator Switches

Decorator switches provide a sleek and appealing look. They are the perfect finishing touch to complement any interior. Easy to use; simply press the rocker. Nightlight and illuminated switches help light the way to see where you are going, increasing security and safety.

- · Smooth, quiet rocker
- · Self-grounding feature is standard
- Ultrasonically welded cover and base provides maximum strength
- · Nightlight and illuminated versions available
- Multiple-drive Slot/Phillips/Robertson head screws
- Operating temperature: -20°C to 60°C



lvory	Light Almond	White	Gray	Black	Brown








Decorator Quiet Rocker Devices

lvory Light Almond White	RSD115I RSD115LA RSD115W	RSD115ILI RSD115ILLA RSD115ILW	DS120NLIV DS120NLLA DS120NLWH	RSD315I RSD315LA RSD315W	RSD315ILI RSD315ILLA RSD315ILW	RSD415I RSD415LA RSD415W
Rating	15A 120-277V AC	15A 120V AC	20A 120V AC	15A 120-277V AC	15A 120V AC	15A 120-277V AC
Termination	Self-Grounding, Push, Back and Side Wire	Self-Grounding, Push, Back and Side Wire	Self-Grounding, Back and Side Wire	Self-Grounding, Push, Back and Side Wire	Self-Grounding, Push, Back and Side Wire	Self-Grounding, Back and Side Wire
Description	Single Pole	Single Pole Illuminated*	Single Pole with Nightlight**	Three Way	Three Way Illuminated*	Four Way





Ivory Light Almond White	RCD111I RCD111LA RCD111W	RCD101I RCD101LA RCD101W	RCD103I RCD103LA RCD103W	RCD108ITR RCD108LATR RCD108WTR	RCD303I RCD303LA RCD303W	RCD308ITR RCD308LATR RCD308WTR
Rating	15A 120-277V AC	15A 120-277V AC	15A 120-277V AC	15A 120V (switch) 15A 125V (recept.)	15A 120-277V AC	15A 120V (switch) 15A 125V (recept.)
Termination	Self-Grounding, Side Wire	Self-Grounding, Side Wire	Self-Grounding, Side Wire	Self-Grounding, Side Wire	Self-Grounding, Side Wire	Self-Grounding, Side Wire
Description	Three (3) Single Pole Switches	Two (2) Single Pole Switches	Single Pole and Three Way Switch		Two (2) Three Way Switches	Three Way Switch, TR Receptacle





Standard Toggle Switches

Standard toggle switches provide the basic on/off control for home lighting and appliances.

- Quiet snap action mechanism
- Tough thermoplastic with ultrasonically welded cover and base
- Elongated strap for easier wall box mounting
- Single pole, double pole, 3-way and 4-way



lvory	Light Almond	White	Black	Brown








Toggle Switches

Description	Single Pole	Three Way	Four Way
Termination	Grounding, Push and Side Wire	Grounding, Push and Side Wire	Self-Grounding, Side Wire
Rating	15A 120V AC	15A 120V AC	15A 120V AC
lvory Light Almond White	RS115I RS115LA RS115W	RS315I RS315LA RS315W	RS415I RS415LA RS415W



Combination Toggle Switches and Devices

Combination	roggic owitorics and bevi	1003	
Description	Two (2) Single Pole Switches	Single Pole Switch, Tamper-Resistant Receptacle	Single Pole and Three Way Switch
Termination	Self-Grounding, Side Wire	Self-Grounding, Side Wire	Self-Grounding, Side Wire
Rating	15A 120V AC	15A 120V (switch) 15A 125V (recept.)	15A 120V AC
lvory Light Almond White	RC101I RC101LA RC101W	RC108ITR RC108LATR RC108WTR	RC103I RC103LA RC103W







LIGHTING CONTROLS

Saving energy has never been so easy. Sensors control the lights automatically. Occupancy sensors are designed to turn on when you are there, and off when you're not. All are adjustable for delayed off. Vacancy sensors are turned on like an ordinary switch, but automatically turn lights off.

- Occupancy or time-based controls
- Integration with third party energy management
- Daylight harvesting sensors for dimming or to keep lights off when natural light is sensed
- Automatic receptacle control

THE RIGHT TECHNOLOGY FOR THE RIGHT APPLICATION



PASSIVE INFRARED requires a clear, unobstructed line of sight to detect occupancy.



lvory

Light Almond

White







Passive Infrared Occupancy Sensors

Description	Color	Catalog Number
Selectable auto-ON/auto-OFF or manual-ON/auto off operation; 120/277V AC; 3-way capable	lvory Light Almond White	WS2000I WS2000LA WS2000W
Selectable auto-ON/auto-OFF or manual-ON/auto off operation; 120V AC only	lvory Light Almond White	WS1000I WS1000LA WS1000W
Auto-ON/auto-OFF; two circuits; 120V AC only	lvory Light Almond White	WS1020I WS1020LA WS1020W
Manual-ON/auto-OFF operation; two circuits; 120V AC only	lvory Light Almond White	WS1021I WS1021LA WS1021W
Manual-ON/auto-OFF operation; 120V AC only	lvory Light Almond White	WS1001I WS1001LA WS1001W
Manual-ON/auto-OFF operation; 120V AC only, with nightlight	lvory Light Almond White	WS1001NI WS1001NLA WS1001NW



Energy efficiency isn't just good for the environment—it's good for homeowners, too. Dimmers and timers offer real energy savings so you can enjoy significant long-term, ongoing reductions in electric bills. Hubbell offers a range of options for controlling residential energy use. Digital timers provide economic lighting and fan control with just the touch of a finger. LED-compatible dimmers allow you to control lighting levels, offering just the right atmosphere with comfort and convenience.

- · Steel mounting strap
- · Compatible with most LED and CFL
- CEC Title 24 and ASHRAE 90.1 compliant





lvory	Light Almond	White	Gray








LED/CFL Dimmers

Description	Color	Rocker Dimmer S	Slide Dimmer	Loggle Dimmer
LED/CFL 200W, Incandescent/Halogen 600W, 120V AC, 60Hz, single pole/three way	Ivory Light Almond White	LCD150DLA	LCD150SI LCD150SLA LCD150SW	- - -
LED/CFL 150W, Incandescent/Halogen 600W, 120V AC, 60Hz, single pole/three way	Ivory Light Almond White	- - -	- - -	LCD150TI LCD150TLA LCD150TW
LED/CFL 300W, Incandescent/Halogen 600W, 120V AC, 60Hz, single pole/three way, with indicator light	Ivory Light Almond White	LCD300DI LCD300DLA LCD300DW	- - -	- - -
Low Voltage Dimmers				
Description	Color	Rocker Dimmer	Slide Dim	mer
01-10V Low Voltage Loads, 10 A @120V AC, 5 A @277V AC, 60Hz, single pole/three way	lvory Light Almond White	LCD0108DI LCD0108DLA LCD0108DW	LCD010 LCD010 LCD010	8SLA
3 Speed Fan Speed Controls				
Description	Color	Rocker Slide Adjustn	nent Toggle 3-	Speed
1.5A 120V AC, single pole/three way	lvory Light Almond White	RDVFSQFI RDVFSQFLA RDVFSQFW	RAYFS0 RAYFS0 RAYFS0	QFLA
Countdown Timer Wall Switch				
Description	20 Min - OFF	E 10 00 00 60 Min .	OFF 15 00 45 60	0 10 Uma OFF 0 4 0 10



Description	Color	30 Min.: OFF, 5,10, 20, 30	60 Min.: OFF, 15, 30, 45, 60	12 Hrs: OFF, 2,4,8,12
1000W @ 120V AC and 1400W @ 277V AC; 1/6hp	Ivory Light Almond White	DT5030I DT5030LA DT5030W	DT5060I DT5060LA DT5060W	DT5012I DT5012LA DT5012W

Neutral required.

Programmable Timer

1 rogrammable rimer	
Description	Catalog Number
Wall switch programmable timer with astronomical clock, features 3 interchangeable cover colors (gray, light almond & white), 3-way capable, 120V AC	WSTA120
Neutral required.	













TAMPER-RESISTANT RECEPTACLES

Put power where you need it, in style with decorator receptacles. The same quality and performance as standard devices, but with a contemporary style. Tamper-resistant devices prevent accidental insertion of a single item, like pins and keys to help keep children safe. The tamper-resistant mechanism is cam action for smooth insertion of plugs, like it is not even there.

- Patented best-in-class mechanism eliminates plug-in difficulty and TR complaints
- Perfect for residential TR applications involving tenants with limited dexterity or hand strength
- For use in locations requiring tamper-resistant receptacles



FAST & SECURE TERMINATIONS

The XClamp eliminates the need to loop the wire, making it the best solution for either 15 or 20 amp branch circuits.

















Duplex Receptacles, 2 Pole/3 Wire

		Decorator		Standard	
Description	Weather and Tamper-Resistant	Tamper-Resistant	Nightlight (0.5 Lumen)	Weather and Tamper-Resistant	Tamper-Resistant
Termination	Self-Grounding, Push and Side Wire	Self-Grounding, Push and Side Wire	Back and Side Wire	Self-Grounding, Push and Side Wire	Self-Grounding, Push and Side Wire
Rating	15A 125V, NEMA 5-15R			15A 125V,	NEMA 5-15R
lvory Light Almond White	RRD15SIWRTR RRD15SLAWRTR RRD15SWWRTR	RRD15SITR RRD15SLATR RRD15SWTR	DR15NLIV DR15NLLA DR15NLWH	RR15SIWRTR RR15SLAWRTR RR15SWWRTR	RR15SITR RR15SLATR RR15SWTR



				Standa	rd		
Description	Tamper-Res	tant Decorator Weather and Tamper-Resistant		Tamper-Resistant Decorator			r-Resistant
Termination	Self-Ground	ding, Side Wire	Self-Grounding, Side Wire		Self-Grounding, Side Wire		
Rating	15A 125V NEMA 5-15R	20A 125V NEMA 5-20R	15A 125V NEMA 5-15R	20A 125V NEMA 5-20R	15A 125V NEMA 5-15R	20A 125V NEMA 5-20R	
lvory Light Almond White	RRD151ITR RRD151LATR RRD151WTR	RRD201ITR RRD201LATR RRD201WTR	RR151IWRTR RR151LAWRTR RR151WWRTR	RR201IWRTR RR201LAWRTR RR201WWRTR	RR151ITR RR151LATR RR151WTR	RR201ITR RR201LATR RR201WTR	



Description	Color	Catalog Number
Tamper-resistant, 15A 125V, 2 pole/3 wire grounding, 20A circuit rated	Ivory Light Almond White	RR15SITRX RR15SLATRX RR15SWTRX



SPECIALTY RECEPTACLES

More power, better performance for appliances and heavy duty connections.

Recessed receptacles allow you to mount TVs flush or push furniture up against the wall without having to worry about the plug getting damaged or dislodged.

- Range & dryer power receptacle terminals accept up to #4 AWG conductors
- Power outlets are suitable for copper or aluminum conductors
- · Wires hidden with clean flush look
- UL Listed and CSA Certified

ROCK & LOCK-EASY AS 1-2-3

Speed up installations with rock and lock self-alignment.















Range and Dryer Power Receptacles, 3 Pole/4 Wire

Description	Color	Flush Mount Surface Mount
30A 125/250V, NEMA 14-30R, 3 pole/4 wire with ground	Black	RR430F RR430
	White	RR430FW -
FOA 105/050V NEMA 14 FOD 2 pole/4 wire with ground	Black	RR450F RR450
50A 125/250V, NEMA 14-50R, 3 pole/4 wire with ground	White	RR450FW -





Black White

Tamper-Resistant Recessed Receptacles, 2 Pole/3 Wire

Description		Color	Catalog Number
	Single gang	lvory Light Almond White	RR1510I RR1510LA RR1510W
Recessed duplex receptacle, 15A 125V, NEMA 5-15R, 2 pole/3 wire, grounding, side wire terminations	2-gang with feedthrough	lvory Light Almond White	RR1512I RR1512LA RR1512W
	2-gang with snap fit	lvory Light Almond White	RR1514I RR1514LA RR1514W
Clock hanger, 15A 125V, NEMA 5-15R, 2 pole/3 wire, grounding, back and side wire terminations		lvory White	RR151CHITR RR151CHWTR





Ivory

Light Almond White

Brown



GFCI & AFCI RECEPTACLES

Safety plus more. Tamper-resistant and self-testing for the utmost in protection. GFCIs are people protection, eliminating power when there is an unintended path to ground. Required in most areas of the home where water may be present.

AFCIs help protect against fire, eliminating power when it senses an arc, occurring when there is a damaged wire or cord set inserted into the outlet. Easily added to most living areas and bedrooms in the home for added protection.

GFCI and AFCI receptacles are required by the NEC in specific rooms in the home. They are great for providing added safety and protection with point of use test and reset.

- GFCI devices feature patented AUTOGUARD® technology
- · Thermoplastic nylon housing
- Clear visual indication of status
- Protection against line and load reversal



lvory	Light Almond	White	Gray	Black	Brown







GFCI Receptacles

Rating	Color	Standard	Tamper-Resistant	Nightlight Two LED Nightlights	Weather and Tamper-Resistant
15A 125V NEMA 5-15R	Ivory Light Almond White	GF15I GF15LA GF15W	GFT15I GFT15LA GFT15W	GFTRST15INL GFTRST15LANL GFTRST15WNL	GFTW15I GFTW15LA GFTW15W
20A 125V NEMA 5-20R	lvory Light Almond White	GF20I GF20LA GF20W	GFT20I GFT20LA GFT20W	GFTRST20INL GFTRST20LANL GFTRST20WNL	GFTW20I GFTW20LA GFTW20W

Dual Function AFCI/GFCI Receptacles

Rating	Color	Standard	Rating	Color	Standard
15A 125V NEMA 5-15R	lvory Light Almond White	AFGF15TRI AFGF15TRLA AFGF15TRW	20A 125V NEMA 5-20R	Ivory Light Almond White	AFGF20TRI AFGF20TRLA AFGF20TRW

AFCI Receptacles

Rating	Color	Standard	Rating	Color	Standard
15A 125V NEMA 5-15R	lvory Light Almond White	AFR15TRI AFR15TRLA AFR15TRW	20A 125V NEMA 5-20R	Ivory Light Almond White	AFR20TRI AFR20TRLA AFR20TRW



SURGE PROTECTION

Surge devices manage power quality and help protect electronics. Receptacles give you point of use protection, while panel protection is specifically designed to catch incoming power variations from outside the home.

- Thermoplastic component shield protects the printed circuit board from contaminants
- All glass, conformal coated PC board provides superior moisture immunity for longer life in humid environments
- Distinctive surge symbol provides quick visual identification
- · Surge protection indicator light
- Muting screw allows damage-alert alarm to be silenced until device is replaced
- Alarmed and non-alarmed versions



Ivory Light White Gray Almond







Circuit Guard® Duplex Receptacles

240 joules, 15kA peak current	White	HBL5260WSA	HBL5262WSA	IG5262WSA
	Light Almond	_	HBL5262LASA	_
Specification surge protection receptacle,	lvory	HBL5260ISA	HBL5262ISA	IG5262ISA
Description	Color	With light	With light and alarm	with light and alarm
				Isolated ground



Wired-In High Quality Surge Protective Device (Type 1 SPD)

Service Voltage V AC	Configuration	Catalog Number
120/240 single phase; mounts to panel	1Phase, 3-wire + Ground	HBL3W50





CHARGING SOLUTIONS

Wireless Chargers

Hubbell's line of wireless wall mount chargers provide more ways to charge faster. Available in single and in combination with a high power Type A&C USB, Hubbell provides both USB and electrical power in a standard single gang opening. Designed to provide maximum charging for portable electronics, the USB ports are capable of charging two tablets simultaneously.

- Flexible holder to hold phone firmly in place
- · Phone can be inserted vertically or horizontally
- Green LED indicates power available and blue LED indicates wireless charging
- Available in combination with 15A or 20A 125V tamperresistant receptacle with USB





Two inductive coils for optimum target area and charging



Easy single gang outlet replacement







Wireless Chargers

Description	Color	Rating	Receptacle	Catalog Number
Wireless wall mount phone charger	White	Coil: 7.5 watt inductive, 125V AC input	_	USB1518



Combination Wireless Chargers

Description	Color	Rating	Receptacle	Catalog Number
Combination wireless wall mount phone charger, inductive coil with USB Type A&C ports, and tamper-resistant receptacle	White	Coil: 7.5 watt inductive, USB: 5A 5V DC Input: 125V AC	15A 125V 20A 125V	USB1528AC USB2028AC



The 'Qi' symbol is a trademark of the Wireless Power Consortium.

USB Charging Receptacles

More ways to charge faster with Hubbell's line of USB chargers, available in Type C, Type A&C or the legacy Type A, all with a USB power output from 2 to 5 amps. Hubbell's USB charger duplex receptacle provides both USB and electrical power in a standard single gang opening. Designed to provide maximum charging for portable electronics, the USB ports are capable of charging two tablets simultaneously.

The 4 port charger outlets feature a USB port door, which enables power when open. When closed, all power is switched off. This eliminates all current flow for a "zero" no-load draw. Buildings looking to provide 100% green efficiency in power delivery will maximize LEED and energy efficiency design.

- LED indicator light for available USB and line voltage power
- USB stainless steel ports rated for minimum 10,000 insertions and removals
- Complies with battery charging specification BC1.2



lvory	Light Almond	White	Gray	Black	Brown







USB Charging Receptacles

Description		Color	15A 125V	20A 125V
USB charger duplex receptacle, 3.1 amp USB output, USB ports rated 10,000 cycles	Two Type A port configurations	Ivory Light Almond White	USB15AI USB15ALA USB15AW	USB20AI USB20ALA USB20AW
	One Type A and one Type-C port configuration	Ivory Light Almond White	USB15ACI USB15ACLA USB15ACW	USB20ACI USB20ACLA USB20ACW



Specialty USB Charging Receptacles

Description	Color	Catalog Number
Switch combo outlet, two USB Type A ports, 2.1 Amp, 5 Volt DC, Style Line® decorator	lvory Light Almond White	USB102I USB102LA USB102W
USB charger 4 port outlet, two USB Type A ports & two Type-C ports, 5 Amp, 5 Volt DC, Style Line® decorator	lvory Light Almond White	USB4ACI USB4ACLA USB4ACW





POWER DELIVERY SOLUTIONS

Countertop Receptacles

Hubbell pop-up receptacles provide a power source ideal for kitchen and bath counters and islands. The first pop-up receptacles UL listed for countertop applications, the receptacles feature Hubbell's patent pending silicone gaskets and patented cam action tamper-resistant technology, .

- First pop-up receptacles UL listed for countertop applications and permanent installations
- Minimizes space required on the countertop and underneath in the cabinet area



BECAUSE SPILLS HAPPEN



UL 498 Section 146-151

Built and listed to be water resistant to a half gallon of liquid spilled on the device.

NEC 406.5(E)

Receptacle assemblies for installation in countertop surfaces shall be listed for countertop application.



9 / 50 0








Countertop Receptacles

			15A 125V Receptacle		20A 125V	Receptacle
Description	Finish	Color/Material	Surface Mount	Flush Mount	Surface Mount	Flush Mount
Tamper-resistant pop-up kitchen counter	Powder Coated	Black White Bronze	RCT200BK RCT200W RCT200BZE	RCT201BK RCT201W RCT201BZE	RCT220BK RCT220W RCT220BZE	RCT221BK RCT221W RCT221BZE
receptacle, rated for 20A circuits Cover: machined aluminum, wiring chamber accepts ½" MC or non-metallic sheath cable	Brushed	Aluminum Brass Nickel	RCT200ALU RCT200BR RCT200NI	RCT201ALU RCT201BR RCT201NI	RCT220ALU RCT220BR RCT220NI	RCT221ALU RCT221BR RCT221NI
	Polished	Chrome	RCT200CH	RCT201CH	RCT220CH	RCT221CH
Tri-Power AC, includes: tamper-resistant pop- up kitchen counter receptacle, USB Type AC	Powder Coated	Black White Bronze	RCT600BK RCT600W RCT600BZE	- - -	RCT620BK RCT620W RCT620BZE	_ _ _
and wireless inductive, rated for 20A circuits Cover: machined aluminum, wiring chamber accepts ½" MC or non-metallic sheath cable; surface mount only	Brushed	Aluminum Brass Nickel	RCT600ALU RCT600BR RCT600NI		RCT620ALU RCT620BR RCT620NI	_ _ _
Surface mount only	Polished	Chrome	RCT600CH	_	RCT620CH	_



Under Cabinet/Counter Power Distribution

Description	Material	Slim Box	GFCI Fit Box
Under cabinet power distribution box, accepts any decorator style device, mounting hardware included	Stainless Steel White Metal White Nylon	RU100SS RU100W RU170W*	RU200SS RU200W RU270W*





Residential Floor Boxes

Residential floor box receptacles offer an economical solution to bring power where you need it. Available in configurations for either slab on grade or wood subflooring, they come in multiple finishes to blend in.

- · Available in surface mount or flush fit
- Pre-assembled flange and cover for fast installation
- Removable neoprene gaskets allow for independent use of either side of the receptacle with the cover closed
- Optional low voltage divider provides for power and voice/data in a compact space
- Back and side knockouts for proper wiring access
- Recessed receptacle minimizes plug protrusion; allowing furniture to be located over the plug
- · Top screw fastening or side joist mounting options









Floor Boxes for Structural Wood Floors

Almond

Black

Chestnut

Brown

Description	Rating	Finish	Cat. Number	Finish	Cat. Number	Finish	Cat. Number
Decorator duplex floor box kit; steel box, flange and door assembly, mounts to subfloor or joists	15A 125V receptacle	Solid Brass Stainless Paint Almond Paint		Black Paint Chestnut Brown Paint Brass Plated	RF515BK RF515BN RF515BP	Chrome Plated Copper Plated Nickel Plated	RF515CH RF515CU RF515NI
	4. 11.11.11						

Copper

Nickel

Chrome



Floor Boxes for Concrete Floors

Stainless

1 1001 Boxes for Concrete 1 10013				
Description	Finish	Catalog Number	Finish	Catalog Number
Flange and hinged door cover assembly, includes	Brushed Aluminum Brushed Brass Plated	RF406ALU RF406BP	Almond Nylon Black Nylon	RF406AL RF406BK
tamper-resistant duplex 15A 125V NEMA 5-15R receptacle	Solid Brass	RF406BR	Chestnut Brown Nylon Gray Nylon	RF406BN RF406GY
PVC floor box, includes round box max 6-inch (4-7/8 in. diam closure plugs, and concrete cover with locator flag	reducers,	Gray	RF400	



Aluminum Brass Almond Black Chestnut Gray



Brass

STRUCTURED WIRING

Non-Metallic Enclosures

The network solution that satisfies the need for dependable and flexible management of your voice/data and entertainment multimedia systems. This modular system makes it easy to upgrade, and keep pace with evolving technologies. Cabinets mount surface or recessed, between 16" studs. All are manufactured from a high impact thermoplastic that virtually eliminates the signal attenuation associated with traditional metal residential enclosures. Hinged cover can be mounted to swing from either side. Provisions to mount optional power outlets and lock kits.

- · Hinged cover can be mounted to swing from either side
- Horizontal and vertical module mounting holes provide maximum flexibility
- Additional nylon push pins assist module mounting
- · High-impact thermoplastic to minimize WiFi degradation









netSELECT® Non-Metallic Network Enclosures

		Dime	nsions: Inches	Module Unit		
Description		Height	Width	Depth	Capacity	Catalog Number
14-inch	With hinged vented door	16.2" (412)	17.5" (445)	4.35" (111)	5	NSOBXP14
	14" height box only	13.5" (343)	17.1" (434)	3.95" (100)	5	NSOBXP14B
network enclosure	Hinged vented door	16.2" (412)	17.5" (445)	0.4" (10)	_	NSOBXP14D
28-inch	With hinged vented door	30" (762)	17.5" (445)	4.35" (111)	11	NSOBXP28
	28" height box only	27.7" (704)	17.1" (434)	3.95" (100)	11	NSOBXP28B
network enclosure	Hinged vented door	30" (762)	17.5" (445)	0.4" (10)	_	NSOBXP28D
42-inch	With hinged vented door (2-piece)	45.1" (1146)	17.5" (445)	4.35" (111)	16	NSOBXP42
network enclosure	42" height box only	42.6" (1082)	17.1" (434)	3.95" (100)	16	NSOBXP42B
	Hinged vented door (2-piece)	45.1" (1146)	17.5" (445)	0.4" (10)	_	NSOBXP42D



Network Modules

Modular components enable your design to match your performance requirements. Modules snap horizontally or vertically into the enclosures for optimum space management.

- Completely enclosed high-impact thermoplastic housing
- High performance Cat6 supports up to 5GBASE-T speeds
- UL and cULus Listed 1863
- All data and phone modules
- TIA-568A wired









Network Modules

Network Modules	
Description	Catalog Numbe
Combination Module 6-port telephone panel, 6-port coaxial splitter, and 6-port Category 5e panel; provides voice, video, and data distribution in a space efficient package; perfect for use with NSOBOX10 and NS790xx plates to quickly establish a comprehensive home network	NSOTVDM6
Primary Telephone Module B-port phone outlets to manage up to (4) incoming lines for voice or accessory applications in a protected PCB module; BJ31X interface jack included for security system connection; RJ45 jack interfaces with optional NSOETM8 telephone expansion nodule for additional extensions.	NSOPTM8
Data Module Category 6 data module, 8-port supports enhanced transmission speeds beyond Gigabit Ethernet; future-proof for omorrow's applications	NSODM8C6
6-Way Coaxial Splitter Module IGHz, basic unit with one incoming line and six outgoing	NSOVM6
Fixed Video Amplifier Module Provides 10dB video signal amplification for incoming cable feeds; recommended for use when more than four outputs are installed or when signal level is low; provides 10dB forward path gain and supports current digital cable systems and modems with a passive return; pre-mounted push pins snap the module quickly into place; includes RG-59 cable umper to connect amplifier to passive video splitter	NSOVAMP
Blank Module Bracket Allows mounting of active components (i.e. switches, routers) or other devices onto a modular platform; (2) VELCRO® brand asteners included to mount components onto module; pre-mounted push pins snap the module quickly into place; 2-pack	NSOBM2
Multi-Provider Patchable Telecom Module 12-port telephone module distributes 4 incoming lines out to 12 locations through RJ-45 jacks; allows data lines to be	NSOMTM12



converted to voice with the move of a patch cord; RJ31X interface jack is included for security system connection

ENTERTAINMENT SYSTEMS

Flat panel TV installations demand the best connections to assure optimum image quality. Hubbell has engineered a metal recessed enclosure that accommodates connections for HDMI, DVI, RG6/UQ and VGA, allowing large, high density cables to fit in the smallest footprint possible. Compatible with a wide variety of TV mounts, this FPTV enclosure provides an in-wall, structured network for multimedia connections and cables.

- Optimal screw-on cover reduces tampering and protects connections
- Mounts to sheetrock or studs

IN-WALL DELIVERY OF MULTIMEDIA & POWER



Enclosure with 15 amp duplex receptacle kit for power

Enclosure scenarios: - Cat 6 jack

- for smart TV
- Double HDMI with wallplate

Cabling scenarios:

- Device-to-device HDMI cable
- Two HDMI in-wall cables

Alternate output available for connection to other equipment (computers, gaming systems, etc.)

Connection scenarios:

- Coax cable in from provider
- Dual HDMI
- RCA component video from source electronics and auxiliary equipment








1

FPTV Connection Enclosures

Description	Catalog Number
2-gang in-wall enclosure, white, 8.16" x 7.92" x 3.37" 4-gang in-wall enclosure, white, 14.80" x 7.92" x 3.37" New work stud brackets	NSAV62M NSAV124M NSAV6NW



	Н	HDMI frame			Snap fi	t connectors	
Surge protected power kit	1-port	2-port		HDMI	F-connector	Cat 5e jack	Cat 6 jack
NSOKPS	NS801W	NS802W		SFHC14W	NSF70W	NSJ5EW	NSJ6W



Description	on	1 ft.	3 ft.	5 ft.	7 ft.	10 ft.	15 ft.	
Blue	Cat. 5e Cat. 6	NSC5EB01 NSC6B01	NSC5EB03 NSC6B03	NSC5EB05 NSC6B05	NSC5EB07 NSC6B07	NSC5EB10 NSC6B10	NSC5EB15 NSC6B15	



Description	3 ft.	6 ft.	10 ft.	15 ft.	20 ft.	25 ft.	30 ft.
HDMI Device Patch Cords	HDPC03BK	HDPC06BK	_	_	_	_	_
Horizontal Cords (Connector to Connector)	_	_	HDH10BK	HDH15BK	HDH20BK	HDH25BK	HDH30BK



Description	Catalog Number
2-gang box, metal, 2" KO, 54 in ³ capacity; 4.21" x 4.06' x 4.00" Low voltage AV wallbox partitions; solid divider; use with HBL985	HBL985 HBL989
2-gang nail-on box, thermoplastic, blue	RR1500










VOICE/DATA CONNECTIONS

Allows for the custom creation of multimedia outlets and workstations while maintaining a decorative look. Multimedia face plates offer a perfect match to electrical wallplates for a consistent finished look.

- Screw terminal or 110 punch down options
- · Decorator and traditional styling available
- · High impact thermoplastic

HDMI OVER HDBaseT AV DISTRIBUTION









Ivory

Light Almond



Molded-In Decorator Frames Voice & Low-Speed Data

Description	One RJ11 jack, 6-position, 4-conductor	Duplex RJ11 jacks, 6-position, 6-conductor	Single F-Connector, Female to Female	Double F-Connector, Female to Female	One Cat. 5e, one F-Connector, Female to Female
Termination	Screw Terminations	Screw Terminations	Screw Terminations	Screw Terminations	110 Punch-Down
lvory Light Almond White	NS770I NS770LA NS770W	NS772I NS772LA NS772W	NS780LA NS780W	_ NS782LA NS782W	NS785LA NS785W



	One F-Conne	ector, one RJ11 jack	Single F-Connector,	Double F-Connector.	One RJ11 jack,
Description	6-position, 6-conductor	6-position, 4-conductor	Female to Female	Female to Female	6-position, 4-conductor,
lvory	NS748I	NS747I	NS750I	NS752I	NS730I
Light Almond	NS748LA	NS747LA	NS750LA	NS752LA	NS730LA
White	NS748W	NS747W	NS750W	NS752W	NS730W



Color	1-Port	2-Port	3-Port	4-Port	6-Port
lvory	NSP11I	NSP12I	NSP13I	NSP14I	NSP16I
Light Almond	NSP11LA	NSP12LA	NSP13LA	NSP14LA	NSP16LA
White	NSP11W	NSP12W	NSP13W	NSP14W	NSP16W

Unloaded 1-Gang Decorator Frames

Description	1-Port	2-Port	3-Port	4-Port	6-Port	Adapter .406" Dia. Hole	Adapter Blank
lvory	NS611I	NS612I	NS613I	NS614I	NS616I	NS621I	NS620I
Light Almond	NS611LA	NS612LA	NS613LA	NS614LA	NS616LA	_	NS620LA
White	NS611W	NS612W	NS613W	NS614W	NS616W	NS621W	NS620W







WALLPLATES

Polycarbonate Wallplates

Made of polycarbonate thermoplastic, the wallplates start out as a clear material, offering excellent color matching—with 375 color and size configurations to choose from. The material is nearly unbreakable and tough enough to withstand repeated high impact and also flexible enough to compensate for wall irregularities during installation.

- · Smooth satin finish
- Pre-inserted captive screws for faster assembly
- Enhanced resistance to heat, humidity, and chemicals



lvory	Light Almond	White	Gray	Black	Brown







Decorator Wallplates

	1	-Gang	2-Gang		3-Gang		4-Gang	
Description	Standard	Mid-size	Standard	Mid-size	Standard	Mid-size	Standard	Mid-size
lvory Light Almond White	P26I P26LA P26W	PJ26I PJ26LA PJ26W	P262I P262LA P262W	PJ262I PJ262LA PJ262W	P263I P263LA P263W	PJ263I PJ263LA PJ263W	P264I P264LA P264W	PJ264I PJ264LA PJ264W



Toggle Switch Wallplates

Description	1-Gang	2-Gang	3-Gang	4-Gang	
lvory Liaht Almond	P1I P1LA	P2I P2LA	P3I P3LA	P4I P4LA	
White	P1W	P2UA P2W	P3W	P4LA P4W	

Duplex Receptacle Wallplates

	-	-
Description	1-Gang	2-Gang
lvory Light Almond White	P8I P8LA P8W	P82I P82LA P82W




Combination Wallplates

		2-Gang		3-	Gang
Description		1-Duplex, 1-Decorator			2-Toggle, 1-Decorator
lvory	P18I	P826I	P126I	P28I	P226I
Light Almond White	P18LA P18W	P826LA P826W	P126LA P126W	P28LA P28W	P226LA P226W

Single Receptacle Wallplates

	1-Gang		2-Gang
	1-1.40in. 1-2.16in.		1-2.16in.
Description	Dia. Hole	Dia. Hole	Dia. Hole
Ivory	P7I	P724I	P703I
Light Almond	P7LA	_	_
White	P7W	P724W	P703W



Additional sizes and colors available.

Snap-on Wallplates

Snap-on wallplates offer a clean, elegant look that can be installed in seconds. The two piece construction includes a subplate that attaches to the device and a screwless cover plate securely held by four snaps. For multiple gang configurations, the subplate aligns the device so that the coverplate matches perfectly.

- · Smooth satin finish
- · Virtually unbreakable
- Easy to snap-on
- Multi-gang auto alignment











Snap-On Decorator Wallplates

Description	1-Gang	2-Gang	3-Gang	4-Gang
lvory	NPS26I	NPS262I	NPS263I	NPS264I
Light Almond	NPS26LA	NPS262LA	NPS263LA	NPS264LA
White	NPS26W	NPS262W	NPS263W	NPS264W



Chap Ch Dapi	ox a reggie manpi	4.00		
Description	1-Gang Duplex	1-Gang Toggle	2-Gang Toggle	3-Gang Toggle
lvory	NPS8I	NPS1I	NPS2I	NPS3I
Light Almond	NPS8LA	NPS1LA	NPS2LA	NPS3LA
White	NPS8W	NPS1W	NPS2W	NPS3W



OUTDOOR SOLUTIONS

Weather Resistant Devices

Hubbell Wiring Device-Kellems has unveiled another industry first: its weatherproof switch, available in three colors, to ensure built-in performance and style in any new or updated outdoor living environment. Unsightly weatherproof covers are no longer needed to protect switches from the elements. A snap-on wallplate provides additional protection with an aesthetically pleasing finish. The result is a device that's meant to get wet and withstand cleaning.

- Rated 3R for outdoor exposed environments*
- Complies with NEC wet and damp installations
- · Internal bellows system seals out water



lvory	Light Almond	White	Gray	Black	Brown







Decorator Weatherproof Series

Description	Color	Catalog Number
Style Line® rocker, weatherproof, self-grounding, 20A, 120/277V AC, back and side wire	Gray Light Almond White	RSD120WPGY RSD120WPLA RSD120WPW





Weather Resistant USB Charging Receptacles

Weather Resistant Gob Gharging Receptacies					
Description		Color	15A 125V	20A 125V	
Tamper-resistant USB charger duplex receptacle,	One Type A and one Type-C port configuration	Gray Ivory Light Almond White	USB15AC5GYWR USB15AC5IWR USB15AC5LAWR USB15AC5WWR	USB20AC5GYWR USB20AC5IWR USB20AC5LAWR USB20AC5WWR	
high power 5 amp 5 volt USB output, USB ports rated 10,000 cycles	Two Type C port configurations	Gray Ivory Light Almond White	USB15C5GYWR USB15C5IWR USB15C5LAWR USB15C5WWR	USB20C5GYWR USB20C5IWR USB20C5LAWR USB20C5WWR	

lvory	Light Almond	White	Gray	Black	Brown



Weather resistant USB devices require the use of an outdoor/while-in-use cover to maintain 3R rating.

Weather Resistant Covers

NEMA 3R rated Extra Duty non-metallic while-in-use covers offer weather protection for outlets when they are in use. High impact polycarbonate construction provides maximum durability and longevity. Available in aesthetically pleasing low profile.

- · Meets the Extra Duty rating
- · Can be installed for new or old work
- · Compatible with common siding types and materials
- · Mounts horizontally or vertically









EXTRA DUTY® Non-Metallic While-In-Use Covers

Description		Dimensions Height x Width x Depth	Catalog Number
1-gang box with clear cover, for horizontal or vertical mounting; 16-in-1 configurations	Standard size Extra deep	5.90" x 4.18" x 2.75" 5.92" x 4.20" x 4.75"	
Standard size 2-gang box with clear tinted cover, for horizontal or vertical mounting; 55-in-1 configurations		5.54" x 5.43" x 2.75"	RW58750



EXTRA DUTY® Recessed Non-Metallic While-In-Use Covers

Description	Housing Color	Catalog Number
1-gang weatherproof recessed clear while-in-use cover, for horizontal or vertical mounting	Gray White Brown	RW5420CG RW5420CW RW5420CZ

Gray White Brown

Weather Resistant Recessed Receptacle with While-In Use Cover

Description	Housing Color	Horizontal Mount	Vertical Mount
Weather and tamper-resistant duplex receptacle with clear while-in-use cover, 15A 125V	Gray	RW15300GY	RW15400GY
	White	RW15300W	RW15400W
	Brown	RW15300BR	RW15400BR

Gray White Brown





ELECTRIC VEHICLE CHARGING STATION

The HBLEV30B Electric Vehicle Charging Station enables fast level 2 charging of any SAE J1772 compatible electric vehicle. This new EV charger delivers power and offers a more compact, easy to use and easy to install solution to electric vehicle charging.

Compatible with all Electric Vehicle Supply Equipment (EVSE) Codes, Standards and Recommended Practices, including SAE J1772, NEC 625, UL 2231 and UL 2594.

- Water-resistant enclosure is rated UL Type 3R/S for indoor and outdoor use
- Amperage selector (15A, 20A, 30A) to meet charging needs
- Time delay feature to delay charge times for more economical rates
- Auto-reset feature enables charging to restart following a minor fault, reducing the chance of having an undercharged battery
- · Status indicator light alerts for power, charging status, and faults





Hardwire installation







Electric Vehicle Charging Station, Hardwired

Description	Catalog Number
EV charging station; 30A 208-240V AC, 7.2 kW output, wall mount; 20 ft. charging cable; hardwire installation	HBLEV30BHW



Description	Catalog Number
EV charging station; 30A 208-240V AC, 7.2 kW output, wall mount; 20 ft. charging cable; NEMA plug installation	HBLEV30B





Complete Electrical Solutions

From wet locations to extreme temperature zones and even corrosive environments, Hubbell solutions meet the challenging conditions of the contruction industry. Improve efficiency and increase safety. Contact us today.



Spider® Boxes

Temporary Power

Sets the safety and performance standard for construction site power needs



Flip Covers

Waterproof Covers

Industry's only 316 stainless steel 4X waterproof covers



inREACH™ Cord Reels

Cable Management

Stainless steel or watertight versions available



SNAPConnect® Devices

Modular Wiring Devices

Our labor-saving receptacles and switches save up to 5 minutes per device.

ONLINE RESOURCES

The Hubbell Wiring Device-Kellems website offers fast and convenient information through our online catalog, technical support, videos and more. Visit www.hubbell.com/wiringdevice-kellems.

CONTACT US

Count on Hubbell Wiring Device-Kellems for the most reliable and innovative wiring device product line in North America.



custserv@hubbell.com




(800) 288-6000



Find your local representative at www.hubbell.com/wiringdevice-kellems

LITERATURE SUPPORT

Hubbell offers an extensive literature library for product support. Downloadable PDFs are available online.



Full Line Catalog



Tri-Power Counter Top Receptacles



Property Management



inREACH™ Cord Reels





hubbell.com/wiringdevice-kellems