

USB Charging Receptacles Type-C • Type A&C • Type A

HUBBELL®
Wiring Device-Kellems

Charger Outlets

Next Generation
in Technology
USB Type-C



The Charging Choice



Type-C



Type A&C



Type A

Charge Faster with Hubbell



USB Charging Receptacles

Type-C • Type A&C • Type A

HUBBELL®
Wiring Device-Kellems

Hubbell USB Chargers are available in the new Type-C port, a combination unit with Type A and C, and the legacy Type A, all with more power. The increase in power to a 5 Amp 5 Volt USB port adds capacity so that there is always ample current to support multiple device charging. Portable mobile manufacturers recently announced products using the faster Type-C ports. More phones, tablets and other electronic devices are expected to use this new standard.

The USB Charger delivers USB power eliminating the need for adapters, while maintaining electrical outlets for higher current requirements. The new USB standard Type-C port supports faster mobile device charging. Hubbell offers more charging options with Type-C and Type A USB configurations.

USB Charger Features

- Compliant with USB BC1.2 Battery Charging and 3.0 Power delivery. Compatible with USB 2.0, 3.0 and 3.1 devices.
- USB Type-C port is legacy USB Type A compatible (with adapter cord - not included).
- Heavy duty stainless steel USB ports; rated for 10,000 cord insertions and removals.
- Patented Hubbell Tamper-Resistant technology uses cam action shutters. When two plug blades are inserted the interlocked cams slide an insulating barrier out of the way. The friction-free design of the mechanism's doors requires much less force, allowing the plug to slide in effortlessly.
- Designed for commercial, industrial and home use.



USB Charger Type-C

Description	Color	15A 125V	20A 125V
USB Charger Outlet:	Black	USB15C5BK	USB20C5BK
two Type-C port configurations,	Brown	USB15C5	USB20C5
high power 5 Amp, 5 Volt USB output,	Gray	USB15C5GY	USB20C5GY
USB ports rated 10,000 cycles	Ivory	USB15C5I	USB20C5I
Commercial Grade Tamper-Resistant duplex receptacle	Light Almond	USB15C5LA	USB20C5LA
	White	USB15C5W	USB20C5W



USB15C5W

USB Charger Combination Type A&C

Description	Color	15A 125V	20A 125V
USB Charger Outlet:	Black	USB15AC5BK	USB20AC5BK
one Type A and one Type-C port configurations,	Brown	USB15AC5	USB20AC5
high power 5 Amp, 5 Volt USB output,	Gray	USB15AC5GY	USB20AC5GY
USB ports rated 10,000 cycles	Ivory	USB15AC5I	USB20AC5I
Commercial Grade Tamper-Resistant duplex receptacle	Light Almond	USB15AC5LA	USB20AC5LA
	White	USB15AC5W	USB20AC5W



USB15AC5W

USB Charger Type A

Description	Color	15A 125V	20A 125V
USB Charger Outlet:	Black	USB15A5BK	USB20A5BK
two Type A port configurations,	Brown	USB15A5	USB20A5
high power 5 Amp, 5 Volt USB output,	Gray	USB15A5GY	USB20A5GY
USB ports rated 10,000 cycles	Ivory	USB15A5I	USB20A5I
Commercial Grade Tamper-Resistant duplex receptacle	Light Almond	USB15A5LA	USB20A5LA
	White	USB15A5W	USB20A5W



USB20A5W

HUBBELL®
Wiring Device-Kellems

www.hubbell-wiring.com

