

**Charge Faster with Hubbell** 



# Hospital Grade • USB Type-C • Type A&C • Type A

Hubbell USB Chargers are available in the new Type-C port, a combination unit with Type A and C, and the legacy Type A, all with more power. The increase in power to a 5 Amp 5 Volt USB port adds capacity so that there is always ample current to support multiple device charging. Portable mobile manufacturers recently announced products using the faster Type-C ports. More phones, tablets and other electronic devices are expected to use this new standard.

The USB Charger delivers USB power eliminating the need for adapters, while maintaining electrical outlets for higher current requirements. The new USB standard Type-C port supports faster mobile device charging. Hubbell offers more charging options with Type-C and Type A USB configurations.

## **USB Charger Features**

- Compliant with USB BC1.2 Battery Charging and 3.0 Power delivery. Compatible with USB 2.0, 3.0 and 3.1 devices.
- USB Type-C port is legacy USB Type A compatible (with adapter cord not included).
- Heavy duty stainless steel USB ports; rated for 10,000 cord insertions and removals.
- Patented Hubbell Tamper-Resistant technology uses cam action shutters. When two plug blades are inserted the interlocked cams slide an insulating barrier out of the way. The friction-free design of the mechanism's doors requires much less force, allowing the plug to slide in effortlessly.

### Hospital Grade USB Charger Type-C

Description	Color	15A 125V	20A 125V	
Hospital Grade USB Charger Outlet:	Black	USB8200C5BK	USB8300C5BK	
two Type-C port configurations,	Brown	USB8200C5	USB8300C5	
high power 5 Amp, 5 Volt USB output,	Gray	USB8200C5GY	USB8300C5GY	
USB ports rated 10,000 cycles	lvory	USB8200C5I	USB8300C5I	
Hospital Grade Tamper-Resistant duplex receptacle	Light Almond	USB8200C5LA	USB8300C5LA	
	Red	USB8200C5R	USB8300C5R	
	White	USB8200C5W	USB8300C5W	

### Hospital Grade USB Charger Combination Type A&C

Description	Color	15A 125V	20A 125V
Hospital Grade USB Charger Outlet:	Black	USB8200AC5BK	USB8300AC5BK
one Type A and one Type-C port configurations,	Brown	USB8200AC5	USB8300AC5
high power 5 Amp, 5 Volt USB output,	Gray	USB8200AC5GY	USB8300AC5GY
USB ports rated 10,000 cycles	lvory	USB8200AC5I	USB8300AC5I
Hospital Grade Tamper-Resistant duplex receptacle	Light Almond	USB8200AC5LA	USB8300AC5LA
	Red	USB8200AC5R	USB8300AC5R
	White	USB8200AC5W	USB8300AC5W

### Hospital Grade USB Charger Type A

Description	Color	15A 125V	20A 125V
Hospital Grade USB Charger Outlet:	Black	USB8200A5BK	USB8300A5BK
two Type A port configurations,	Brown	USB8200A5	USB8300A5
high power 5 Amp, 5 Volt USB output,	Gray	USB8200A5GY	USB8300A5GY
USB ports rated 10,000 cycles	lvory	USB8200A5I	USB8300A5I
Hospital Grade Tamper-Resistant duplex receptacle	Light Almond	USB8200A5LA	USB8300A5LA
	Red	USB8200A5R	USB8300A5R
	White	USB8200A5W	USB8300A5W



www.hubbell-wiring.com







USB8300AC5W



USB8300A5W



Hubbell Wiring Device-Kellems • Hubbell Incorporated (Delaware) • 40 Waterview Drive • Shelton, CT 06484 • Phone (800) 288-6000 • FAX (800) 255-1031 Printed in U.S.A. Specifications subject to change without notice.

