

Is your property tech ready?

Low investment home enhancements with maximum ROI



Wired, wireless and Wi-Fi solutions

Wireless wall-mount phone chargers

More ways to charge faster. Our design provides both USB and electrical power using a standard single gang opening for maximum charging for portable electronics. Available in single and in combination with high-power Type A and C USB ports. Capable of charging two tablets simultaneously.

- Flexible holder holds phone firmly in place
- Insert phone vertically or horizontally
- Green LED indicates power available and blue LED indicates wireless charging
- Available in combination with 15A or 20A 125V tamper-resistant receptacle with USB

Tri-power countertop pop-up receptacles

Provide power and charging, ideal for kitchen and bath counters and islands. The first pop-up receptacles with integrated wireless charging UL Listed for countertop applications. These receptacles feature our exclusive silicone gaskets and cam action tamper-resistant technology.

- Charge multiple devices at the same time
- Spill water tested
- Permanent installation ready (suitable for MC or NMSC cable)
- Minimizes space required on the surface and underneath in the cabinet
- Type A and C USB ports



Reliable, easy to install



Convenient, powerful options

iDevices® smart home products

A truly smart home works for homeowners and keeps them connected. Our advanced smart home products offer an experience of unparalleled comfort, convenience, and security. Give homeowners the power to control their entire living space with the iDevices Connected app, or their voice using Siri®, Amazon Alexa, and the Google Assistant.

- Wi-Fi & Bluetooth enabled
- Guided in-app setup
- Connect direct to home Wi-Fi networks, no separate hub required
- Switches, outlets and thermostats

USB Charger duplex receptacles and outlets

Our USB charger line provides Type C, Type A and C or legacy Type A ports, all with power output from 2 to 5 A. Our USB charger duplex receptacles provide both USB and electrical power in a standard single gang opening. Maximize portable electronics charging with USB ports capable of charging two tablets simultaneously.

- Four port charger features a USB port door to enable power when open, switch it off when closed, eliminating all current flow for maximum energy efficient design.
- LED light indicates available USB and line voltage power
- Stainless-steel USB ports rated for minimum 10,000 insertions and removals
- Complies with battery charging specification BC1.2



Make every day extraordinary



Wiring Device-Kellems

www.hubbell.com/wiringdevice-kellems

Residential Product Highlights

Home Enhancements | Innovation and Convenience from Hubbell

Wireless Wall-Mount Phone Chargers

Description	Rating	Receptacle	Catalog Number
USB combination wireless wall-mount phone charger, white	Coil: 7.5 watt inductive, USB: 5A 5V	15A 125V 20A 125V	USB1528AC USB2028AC
Wireless wall-mount phone charger, white	Coil: 7.5 watt inductive, 125 volt input	-	USB1518



USB Chargers

Description	Configuration	Rating	Catalog Number
Hubbell-Pro USB charger duplex receptacle, 3.1A, 5V USB output, white	(2) Type A ports	15A 125V 20A 125V	USB15AW USB20AW
	(1) Type A port (1) Type C port	15A 125V 20A 125V	USB15ACW USB20ACW
USB 4-port charger outlet, 5A 5V DC, decorator, white	(2) Type A ports (2) Type C ports	-	USB4ACW



Instinct™

Description	Catalog Number
Instinct switch with Amazon Alexa built in, white	IDEV0022



Thermostat

Description	Catalog Number
Thermostat, white	IDEV0005AND5



Outlets, Switches & Dimmers

Description	Catalog Number
Wall Switch, white	IDEV0008HW
Dimmer Switch, white	IDEV0009HW
Instant Switch, white	IDEV0020
Wall Outlet, white	IDEV0010HW



Occupancy & Vacancy Sensors

Description		Rating	Catalog Number
Selectable manual/auto ON operation, white	Dual voltage 120-277V AC; multi-way capable	Standard Nightlight	WS2000W WS2000NW
	120V AC only	Standard Nightlight	WS1000W WS1000NW
Manual ON operation; 120V AC only; CA Title 24 compliant, white		Standard Nightlight	WS1001W WS1001NW
Auto ON operation, dual circuit; 120V AC only, white		Standard Nightlight	WS1020W WS1020NW
Manual ON operation, dual circuit; 120V AC only, white		Standard Nightlight	WS1021W WS1021NW



Countdown & Digital Timers

Description		Catalog Number
Countdown timer; 1000W @ 120V AC; 1400W @ 277V AC, white	30 min: OFF, 5, 10, 20, 30	DT5030W
	60 min: OFF, 15, 30, 45, 60	DT5060W
	12 hrs: OFF, 2, 4, 8, 12	DT5012W



Countertop Pop-Up Receptacles

Description	Flange Color	Top Color	15A 125V	20A 125V
Tamper-resistant pop-up countertop receptacle; rated for 20A circuits, surface mount (flush mount options available)	Black	Black	RCT200BK	RCT220BK
	White	White	RCT200W	RCT220W
	Aluminum	Aluminum	RCT200ALU	RCT220ALU
	Nickel	Nickel	RCT200NI	RCT220NI
Tri-Power tamper-resistant pop-up countertop receptacle; USB Type AC and wireless inductive, rated for 20A circuits, surface mount	Black	Black	RCT600BK	RCT620BK
	White	White	RCT600W	RCT620W
	Aluminum	Black, white or gray	RCT600ALU	RCT620ALU
	Nickel	Black, white or gray	RCT600NI	RCT620NI

