

BURNDY® PATRIOT® PAT81K2 SERIES

FEATURES & BENEFITS



Unique Crimp Guides

81KSMLGUIDEKIT:
Copper #8-4 AWG
Aluminum #8-6 AWG

81KLRGGUIDEKIT:
Copper #3 AWG-#250 kcmil
Aluminum #5-3/0 AWG

MODELS, SPECIFICATIONS & CAPACITIES

MODELS	
PAT81K2U03A2	Tool, Guides, 3Ah, 120V AC, Hard Case
PAT81K2U05A2	Tool, Guides, 5Ah, 120V AC, Hard Case
PAT81K2U03A3	Tool, Guides, 3Ah, 120V AC, Pro Bag
PAT81K2U05A3	Tool, Guides, 5Ah, 120V AC, Pro Bag



Range Taking Capability: #8 AWG to 1000 kcmil



Connections are UL Listed to 486A-486B on Copper & Aluminum terminals and splices

TRUST THE BURNDY® ENGINEERED SYSTEM

SPECIFICATIONS	
Output Force	6 Tons
Tool Weight	12.6 lbs
Size	15.20" x 14.93" x 3.25"
Die Style	Dieless
Operating Voltage	18 V-DC Lithium-ion
Recharge Time	30 minutes (3.0Ah)
	45 minutes (5.0Ah)
Warranty	5 year limited warranty
	Lifetime warranty on INFINITY DRIVE®
	3 years on batteries and charger

CRIMPING CAPACITIES	TERMINALS & SPLICES	HYPLUG™
Copper	#8 AWG - 1000 kcmil	
Copper Flex	#8 AWG - 777.7 kcmil	
Aluminum	#8 AWG - 750 kcmil	#8 AWG - 750 kcmil



BURNDY, LLC

7 Aviation Park Drive
Londonderry, NH 03053

Customer Service
1-800-346-4175

Technical Service
1-800-451-4956

CANADA

1-800-465-7051

MEXICO

011-52-722-265-4400

BURNDY Tool Service Center

Littleton Industrial Park
Littleton, NH 03561
1-800-426-8720

BURNDY TOOLS

PATRIOT® PAT81K2
4-POINT® DIELESS
SERIES



BURNDY

www.hubbell.com



BURNDY