



UNITAP™ Heavy Duty Series

UL 486A-B Listed; #2-750 kcmil Cu/Al Dual Rated

Introduction

We are pleased to announce the addition of a family of Heavy Duty Insulated Multi-tap and In-Line splicer/reducers to our current offering of UNITAP™ connectors. This expansion includes 8 tap configurations and in-line splicer/reducers in both clear and UV-rated black and accommodate wire sizes from #2 - 750 kcmil. Each conductor port contains 2 set screws to increase the strength and performance of the connector, and will provide a reliable and robust connection in the most demanding applications.

Features & Benefits



- 600 Volt Rated
- Fully insulated aluminum 6061-T6 connector body saves time and lowers installation costs by eliminating taping
- Listed to UL 486A-B, File E9498
- Dual Rated for use with copper and aluminum conductors
- Range taking designs accommodate wire sizes from #2 - 750 kcmil
- Configurations include Double-Side Entry Taps in 2 to 12 ports and In-Line Splicer/Reducers
- Available in UV-Rated Black or Clear Plastisol Insulation
- Operating temperature range from -40°C to 135°C
- Conductor ports are pre-filled with oxide inhibitor
- Screw Port and Conductor Port caps provided to protect against contamination and accidental contact of energized parts

Markets

- C & I
- Solar
- Utility
- MRO



Customer Service 1-800-346-4175 | Tool Service Center 1-800-426-8720 | Technical Services 1-800-451-4956 | www.burndy.com