

## HPS-LWMAG Series

### Hydraulic Pole Saws

Light weight, low pressure hydraulic

- Light weight, narrow kerf OREGON® bar with anti-kickback
- Optimized limb hook and chip deflector
- Cartridge style valve
- 2-stage safety trigger, anti-kickback chain and anti-slip grip
- Fiberglass tube tested at final assembly with CHANCE® Hot Stick Tester Model CC403-3178 to the value specified as per OSHA 1910.269

#### Variations:

**HPS1375LWMAG** 75" overall length; 1.25" pole diameter;  
13" cutting capacity;

Weight: 8.75 lbs dry, 11 lbs with oil

**HPS1388LWMAG** 88" overall length; 1.25" pole diameter;  
13" cutting capacity;

Weight: 8.95 lbs dry, 11.2 lbs with oil

#### Specifications:

<b>Flow:</b>	4-8 GPM (16-30 LPM)
<b>Pressure:</b>	1000-2000 PSI (70-140 BAR)
<b>Max. Back Pressure:</b>	250 PSI (17 BAR)
<b>Operation:</b>	Open/Closed Center
<b>Motor:</b>	Gear
<b>Chain:</b>	.325" pitch anti-kickback
<b>Tool Ports:</b>	#6 SAE O-Ring
<b>Warranty:</b>	5 year limited warranty

#### Accessories:

See *Low Pressure Hydraulic Accessories* for additional options

