

PAT444S Series

PATRIOT® 11-Ton C-Head Dieless Tool Hydraulic Self-Contained, 18V Lithium-ion

- New C-Head style for easy access and increased flexibility
- Dieless System with range taking capability
- 355° Head rotation
- Ergonomically balanced
- 3.0Ah and 5.0Ah versions available
- Includes 2 batteries, charger and polymer carrying case
- **EP Enhanced Power** labeled tools accept 2.0, 3.0, 4.0, 5.0, and 6.0Ah Makita batteries

For Use On:

Copper #4 AWG-1000 kcmil

Terminals: YA-L, YA-2LN, YA, YA-2N, YA-L-2TC, YAB-4N,
YA-L-TC, YA-2L, YA-4N

Splices: YS-L, YS, YS-T

Aluminum #4 AWG-1000 kcmil

Terminals: YA-A, YA-A-TN

Splices: YS-A

HYPLUG™: AYP, AYPO

ACSR, AAC, AAAC, ACAR #4 AWG-556.6 kcmil

Splices: YDS-RL

See Expanded Range details in Reference Section

Variations:

PAT444SLI with 3.0Ah Li-Ion batteries

PAT444SL5 with 5.0Ah Li-Ion batteries

Connections are UL Listed to
UL 486A-486B on Copper & Aluminum
terminals and splices;

Also, comply with
ANSI C119.4 on YDS-RL Splices
(ACSR, ACC, AAAC, ACAR)
Other BURNDY splice families
coming soon!




Specifications:

Output Force:	11 Tons
Tool Weight:	16 lbs
Size:	16.9" x 13.7" x 3.2"
Die Style:	Dieless
Operating Voltage:	18 V-DC Lithium-Ion
Recharge Time:	
3.0Ah	30 minutes
5.0Ah	45 minutes
Warranty:	5 year limited warranty Lifetime warranty on INFINITY DRIVE® 3 years on batteries and charger

Accessories:

BAT18VLI:	Hi-capacity LI Makita battery (3.0Ah)
BAT18V5AHLI:	Hi-capacity LI Makita battery (5.0Ah)
PATCHGRLI:	120V-AC Makita charger
PATCHGRLIDC:	12/24V-DC Makita charger
FORCEGAUGE11:	Force Test Gauge



Unique 444S Crimp
Embossment