

# Y122CMR HYTOOL™

BURNDY® is pleased to introduce the new features of the Y122CMR mechanical full cycle ratchet HYTOOL™.

## Y122CMR HYTOOL™



The Y122CMR HYTOOL™ will accommodate copper compression HYDENT™ connectors for :

- #12 - #2 AWG Stranded
- #12 - #2 AWG G, H, I, K, M and DLO Flex
- #12 - #2 AWG Solid

The die index and BURNDY “bug” ( ) are embossed on the crimped connector for permanent inspectability. This tool is also available in 2 different kits (Y122CMRKIT and Y122CMRCIKIT) both come with a sturdy metal carrying case that houses the tool and select terminals.

The Y122CMR ratchet tool provides a full cycle ratchet crimp every time. The Y122CMR will not release until complete. Additionally, the comfort-grip handles reduce operator fatigue during continuous use.

[Click here to view the introductory video on Y122CMR HYTOOL™](#)



## Useful Links

### Product Information

- [Y122CMR HYTOOL™ - Introduction Document](#)
- [Y122CMR HYTOOL™ - Cut Sheet](#)
- [Y122CMR HYTOOL™ - Flyer](#)

### Markets & Applications

- Commercial
- Industrial
- Electronics
- Marine
- Automotive, Truck, Trailer

## Features and Benefits

- Overmolded comfort grip handles
- Easy groove identification with color coded dies
- UL Listed/CSA Certified connections when used with recommended BURNDY terminals/splices
- Die index embossment for all 6 wire ranges
- Emergency release mechanism in case of misalignment or mistaken die choice
- #10/12 Die Index
- D-Ring Lanyard Holder