

# BURNDY® PATRIOT® PAT81K2 SERIES

## FEATURES & BENEFITS



Unique Crimp Guides



**81KSMLGUIDEKIT:**  
Copper #8-4 AWG  
Aluminum #8-6 AWG

**81KLRGGUIDEKIT:**  
Copper #3 AWG-#250 kcmil  
Aluminum #5-3/0 AWG

## MODELS, SPECIFICATIONS & CAPACITIES

### MODELS

PAT81K2U03A2	Tool, Guides, 3Ah, 120V AC, Hard Case
PAT81K2U05A2	Tool, Guides, 5Ah, 120V AC, Hard Case
PAT81K2U03A3	Tool, Guides, 3Ah, 120V AC, Pro Bag
PAT81K2U05A3	Tool, Guides, 5Ah, 120V AC, Pro Bag



TRUST THE BURNDY® ENGINEERED SYSTEM

### SPECIFICATIONS

Output Force	6 Tons
Tool Weight	11.05 lbs (without battery)
Size	15.20" x 14.93" x 3.25"
Die Style	Dieless
Operating Voltage	18 V-DC Lithium-ion
Recharge Time	30 minutes (3.0Ah)
	45 minutes (5.0Ah)
Warranty	5 year limited warranty
	Lifetime warranty on INFINITY DRIVE®
	3 years on batteries and charger



Range Taking Capability: #8 AWG to 1000 kcmil



Connections are UL Listed to 486A-486B on Copper & Aluminum terminals and splices

CRIMPING CAPACITIES	TERMINALS & SPLICES	HYPLUG™
Copper	#8 AWG - 1000 kcmil	
Copper Flex	#8 AWG - 777.7 kcmil	
Aluminum	#8 AWG - 750 kcmil	#8 AWG - 750 kcmil



**WHEN FACING THE UNPREDICTABLE,  
YOU'RE NOT ALONE...**

**BURNDY HAS YOUR BACK!**

**PROFESSIONAL GRADE  
TOOLS YOU KNOW  
TOOLS YOU TRUST**

# BURNDY TOOLS

PATRIOT® PAT81K2  
4-POINT® DIELESS  
SERIES



**BURNDY, LLC**  
7 Aviation Park Drive  
Londonderry, NH 03053

**Customer Service**  
1-800-346-4175

**Technical Service**  
1-800-451-4956

**CANADA**  
1-800-465-7051

**MEXICO**  
011-52-722-265-4400

**BURNDY Tool Service Center**  
Littleton Industrial Park  
Littleton, NH 03561  
1-800-426-8720



[www.hubbell.com](http://www.hubbell.com)

