

BURNDY® PATRIOT® PATCUT1500 SERIES

FEATURES & BENEFITS



MODELS, SPECIFICATIONS & CAPACITIES

MODELS	
PATCUT1500LI	Tool, 3Ah, 120V AC
PATCUT1500L5	Tool, 5Ah, 120V AC
PATCUT1500LCB	Tool, No Charger/Batteries

SPECIFICATIONS	
Tool Weight	6.90 lbs (without battery)
Length	15.5"
Operating Voltage	18 V-DC Lithium-ion
Recharge Time	30 minutes (3.0Ah)
	45 minutes (5.0Ah)
Warranty	3 year limited warranty (excluding blades)
	3 years on battery and charger

CUTTING CAPACITIES	
Aluminum	up to 1500 kcmil
Copper Flex	up to 1250 kcmil
Copper (soft drawn)	up to 1000 kcmil
Copper (hard drawn)	up to 750 kcmil
Do Not Cut Steel or ACSR	



TRUST THE BURNDY® ENGINEERED SYSTEM





BURNDY® TOOLS

PATRIOT®
PATCUT1500
SERIES



BURNDY, LLC

7 Aviation Park Drive
Londonderry, NH 03053

Customer Service
1-800-346-4175

Technical Service
1-800-451-4956

CANADA

1-800-465-7051

MEXICO

011-52-722-265-4400

BURNDY Tool Service Center

Littleton Industrial Park
Littleton, NH 03561
1-800-426-8720



www.hubbell.com

