

Voltages Input	Voltages Output	Available KVA Range	Type of Circuit	Acme Drawing No.
208 Delta	208Y/120	3-75	Isolation	<a href="#">A-125879</a>
208 Delta	208Y/120	3-86	Auto Zig-Zag 1	<a href="#">A-125895</a>
208 Delta	240 Delta/120	1.68-25.2	O.D. ISO	<a href="#">A-700314</a>
208 Delta	240 Delta	3-75	Isolation	<a href="#">A-125880</a>
208 Delta	416Y/240	3-75	Isolation	<a href="#">A-700598</a>
208 Delta	416Y/2240	3-75	Isolation	<a href="#">A-700591</a>
208Y/120	208Y/120	3-75	Isolation	<a href="#">A-125857</a>
208Y/120	374Y/216	22.5-75	Isolation	<a href="#">A-125883</a>
208Y/120	374Y/216	112.5-750	Isolation	<a href="#">A-102730</a>
208Y/120	480Y/277	3-75	Isolation	<a href="#">B-39881-Pg2</a>
240 Delta	208Y/120	3-15	Isolation	<a href="#">A-125855</a>
240 Delta	208Y/120	9-15	Isolation	<a href="#">A-102723</a>
240 Delta	208Y/120	22.5-75	Isolation	<a href="#">A-102722-B</a>
240 Delta	208Y/120	112.5-750	Isolation	<a href="#">A-125856</a>
240 Delta	208Y/120	3-75	Isolation	<a href="#">A-125858</a>
240 Delta	240 Delta	3-75	Isolation	<a href="#">A-125859</a>
240 Delta	240Y/138	10.3-258.75	Auto Zig-Zag 1	<a href="#">A-125896</a>
240 Delta	374Y/216	22.5-75	Isolation	<a href="#">A-125881</a>
240 Delta	374Y/216	112.5-750	Isolation	<a href="#">A-125882</a>
240 Delta	480Y/277	3-75	Isolation	<a href="#">B-39881-Pg1</a>
380 Delta	240 Delta	3-75	Isolation	<a href="#">A-700592</a>
380 Delta	240 Delta	112.5-300	Isolation	<a href="#">A-700593</a>
380 Delta	228 Delta	1.4-7.0	O.D. Auto	<a href="#">A-35633</a>
380 Delta	228 Delta	4.2-7.0	O.D. Auto	<a href="#">A-125892</a>
380 Delta	228 Delta	10.4-34.5	O.D. Auto	<a href="#">A-125893</a>
380 Delta	228 Delta	51-227	O.D. Auto	<a href="#">A-125894</a>
380 Delta	416Y/240	3-75	Isolation	<a href="#">A-700599</a>
380 Delta	416Y/240	112.5-300	Isolation	<a href="#">A-700594</a>
380Y/220	240 Delta	3-75	Isolation	<a href="#">A-700600</a>
380Y/220	240 Delta	112.5-300	Isolation	<a href="#">A-700595</a>
416Y/240	440 Delta	3-75	Isolation	<a href="#">A-700602</a>
416Y/240	440 Delta	112.5-300	Isolation	<a href="#">A-700597</a>
416 Delta	240 Delta	3-75	Isolation	<a href="#">A-700601</a>
416 Delta	240 Delta	112.5-300	Isolation	<a href="#">A-700596</a>
416Y/240	208Y/120	3-15	Isolation	<a href="#">A-700319</a>
416Y/240	208Y/120	22.5-75	Isolation	<a href="#">A-700322</a>
480 Delta	240 Delta/120	1.68-5.04	O.D. ISO Hi-Leg 1	<a href="#">A-125849</a>
480 Delta	240 Delta/120	3.36	O.D. ISO Hi-Leg 1	<a href="#">A-125850</a>
480 Delta	240 Delta/120	5.04	O.D. ISO Hi-Leg 1	<a href="#">A-125851</a>
480 Delta	240 Delta/120	8.4	O.D. ISO Hi-Leg 1	<a href="#">A-125852</a>
480 Delta	240 Delta/120	12.6-25.2	O.D. ISO Hi-Leg 1	<a href="#">A-125853</a>
480 Delta	240 Delta/120	42	O.D. ISO Hi-Leg 1	<a href="#">A-125854</a>
480 Delta	240 Delta/120	63-266	O.D. ISO Hi-Leg 1	<a href="#">A-111702</a>
480 Delta	240 Delta	1.68-8.4	O.D. ISO	<a href="#">A-32817-B</a>

480 Delta	240 Delta	5.04-8.4	O.D. ISO	<a href="#">A-125872</a>
480 Delta	240 Delta	12.6-42	O.D. ISO	<a href="#">A-125873</a>
480 Delta	240 Delta	63-420	O.D. ISO	<a href="#">A-125874</a>
480 Delta	416Y/240	3-15	Isolation	<a href="#">A-125875</a>
480 Delta	416Y/240	9-15	Isolation	<a href="#">A-125876</a>
480 Delta	416Y/240	22.5-75	Isolation	<a href="#">A-125877</a>
480 Delta	416Y/240	112.5-750	Isolation	<a href="#">A-125878</a>
480 Delta	394Y/228	9-15	Isolation	<a href="#">A-125884</a>
480 Delta	394Y/228	22.5-75	Isolation	<a href="#">A-125885</a>
480 Delta	394Y/228	112.5-750	Isolation	<a href="#">A-125886</a>
600 Delta	208Y/120	3-6	Isolation	<a href="#">A-102758</a>
600 Delta	208Y/120	9-75	Isolation	<a href="#">A-125863</a>
600 Delta	208Y/120	112.5-500	Isolation	<a href="#">A-125864</a>
600 Delta	240 Delta	3-6	Isolation	<a href="#">A-125860</a>
600 Delta	240 Delta	9-75	Isolation	<a href="#">A-125861</a>
600 Delta	240 Delta	112.5-500	Isolation	<a href="#">A-125862</a>
600 Delta	240 Delta/120	1.68-2.52	O.D. ISO Hi-Leg 1	<a href="#">A-125865</a>
600 Delta	240 Delta/120	3.36	O.D. ISO Hi-Leg 1	<a href="#">A-125866</a>
600 Delta	240 Delta/120	5.04-25.2	O.D. ISO Hi-Leg 1	<a href="#">A-125867</a>
600 Delta	240 Delta/120	42	O.D. ISO Hi-Leg 1	<a href="#">A-125868</a>
600 Delta	240 Delta/120	63-168	O.D. ISO Hi-Leg 1	<a href="#">A-125869</a>
600 Delta	240 Delta	1.68-3.36	O.D. ISO	<a href="#">A-33227-A</a>
600 Delta	240 Delta	5.04-42	O.D. ISO	<a href="#">A-125870</a>
600 Delta	240 Delta	63-280	O.D. ISO	<a href="#">A-125871</a>