

# Bell & TayMac Hour

## Topic: TayMac/Bell White Color Cover Options

August 25, 2020

**NOTE: For those who are unable to attend we will be recording this training session for future reference and review....**

**PLEASE MUTE YOUR PHONES....**



**COMMERCIAL CONSTRUCTION**



# Products to Cover



## *Nonmetallic & Metallic In-use Covers*

- Nonmetallic In-Use Covers
- Nonmetallic Flat Device Covers
- Nonmetallic Low Profile In-Use Covers
- Nonmetallic Recessed Enclosure Covers
- Metallic Low Profile In-Use Covers
- Nonmetallic Deck Outlet Cover

## *Metallic & Nonmetallic Flip, Blank, Cluster and Decorator Covers*

- Metallic Flip Covers
- Metallic Lampholder/Cluster and Blank Covers
- Metallic Decorator Switch Covers
- Nonmetallic Covers



**COMMERCIAL CONSTRUCTION**





*Nonmetallic & Metallic In-use Covers*



**COMMERCIAL CONSTRUCTION**



# Nonmetallic & Metallic In-Use Covers



**NM In-Use Covers**

**Cat. No. MM420W/MM410W**

- Polycarbonate construction provides maximum durability
- Patented Quick-Fit keyhole mounting system
- Patented Universal Fit Adapter System Technology (U-Fast) for 16-in-1 custom device configurations, comes pre-configured for GFCI
- Horizontal or vertical mount



**NM Flat Device Covers**

**Cat. No. MM110W/MM1410**

- Polycarbonate construction provides maximum durability
- Patented Quick-Fit keyhole mounting system
- Patented Universal Fit Adapter System Technology (U-Fast) for 16-in-1 custom device configurations, comes pre-configured for GFCI
- Horizontal or vertical mount



**NM Low Profile In-Use Covers**

**Cat. No. ML500W/ML450W**

- Revolutionary patented design expands from 1" to 3"
- Ultra-rugged polycarbonate & synthetic neoprene rubber that will not dry rot, crack or deteriorate in sunlight
- Patented Quick-Fit keyhole mounting system and U-Fast adapter system for 16-in-1 custom device configuration



**NM Recessed Enclosure Covers**

**Cat. No. MR420CW**

- Flat profile (recessed) for in-use in wet locations
- Installed for new or old work
- Compatible with all common siding types and materials such as vinyl, wood, stucco and brick/block
- Horizontally or vertically mounted
- Includes electrical box and optional siding flange



**Metal Low Profile In-Use Covers**

**Cat. No. MX4280WH**


- Revolutionary patented design expands from 2" to 3-1/2" for in-use needs
- Heavy duty die-cast metal construction with premium powder coat
- Patented Quick-Fit keyhole mounting system and U-Fast adapter system for 16-in-1 custom device configuration
- Lockable open or closed



**COMMERCIAL CONSTRUCTION**



# Nonmetallic Deck Outlet Cover



**NM Deck Outlet Cover**

**Cat. No. DOC320W**

- Provides convenient power access on raised wood or composite decks and porches
- Low profile design meets ADA standards
- Heavy duty UV-resistant polycarbonate
- Cord hooks hold two power cords in place, including most 16 gauge grounded extension cords
- Fits standard duplex, decorator and GFCI receptacles
- Rain chamber and "drip loop" design provide two levels of in-use protection
- Pre-attached weatherproof gasket keeps water from entering around the self-closing lid



**NM Deck Outlet Cover Kit**

**Cat. No. DOCK320W**

- *One weather/tamper resistant 15A GFCI receptacle*
- *One metal electrical box with ½" threaded outlets and gasket*
- One weatherproof cover constructed of heavy-duty UV-resistant polycarbonate
- Low profile design with beveled edge and slip-resistant texture meets ADA standards
- Rain chamber and "drip loop" design for added protection
- Pre-attached gasket
- Cord hooks hold two power cords (up to 16 gauge) in place
- For use on wood or composite raised decks and porches

**NEW**



**COMMERCIAL CONSTRUCTION**







*Metallic & Nonmetallic Flip, Blank, Cluster and  
Decorator Covers*



**COMMERCIAL CONSTRUCTION**



# Metallic Flip Covers



## Multi-Configuration Flip Covers

**Cat. No. MX1050W / MX2050WH**

- Heavy duty die-cast metal construction with premium powder coat
- Patented Quick-Fit keyhole mounting system and U-Fast adapter system for 12-in-1 custom device configurations
- Lockable tab and spring hinge closure
- GFCI configuration
- Vertical/horizontal device mount



## Metallic Flip Covers

**Cat. No. 5103-1/5101-1**

- Rugged metallic construction
- State-of-the-art powder coat finish
- Self closing lids assure weatherproof protection when the receptacle is not in use
- GFCI configuration
- Vertical (5103-1) and horizontal (5101-1) mount



## Metallic Flip Covers

**Cat. No. 5180-1**

- Rugged metallic construction
- State-of-the-art powder coat finish
- Self closing lids assure weatherproof protection when the receptacle is not in use
- Installation hardware, gasket, and instructions are included
- Duplex configuration
- Horizontal mount



## Metallic Flip Covers

**Cat. No. 5146-1/5155-1**

- Rugged metallic construction
- State-of-the-art powder coat finish
- Self closing lids assure weatherproof protection when the receptacle is not in use
- Duplex (5146-1) and Single 1.406" diameter (5155-1)
- Vertical mount



**COMMERCIAL CONSTRUCTION**



# Lamp holder, Cluster and Blank Covers



**Lamp holder/Cluster Covers**

**Cat. No. 5186-1 / 5189-1**

- Rugged die cast construction
- State-of-the-art powder coat finish provides maximum weatherability and scratch resistance
- Closure plugs included based on one hole or three hole configuration (1/2" outlets)
- Horizontal or vertical mount



**Lamp holder/Cluster Covers**

**Cat. No. 5193-1 / 5197-1**

- Rugged die cast construction
- State-of-the-art powder coat finish provides maximum weatherability and scratch resistance
- Closure plugs included based on one hole or three hole configuration (1/2" outlets)
- Horizontal or vertical mount



**Round Box Covers**

**Cat. No. 5374-1**

- 4 in. Round Blank Cover - Box Mount
- Rugged metallic construction
- State-of-the-art powder coat finish provides maximum weatherability and scratch resistance
- Includes gasket and mounting hardware



**Blank Box Covers**

**Cat. No. 5173-1 / 5175-1**

- Rugged metallic construction
- State-of-the-art powder coat finish provides maximum weatherability and scratch resistance
- Blank Single Gang and 2-Gang options
- Vertical or horizontal mount



**COMMERCIAL CONSTRUCTION**





# Metallic Decorator Switch Covers



**1-Gang Decorator Switch Cover**

**Cat. No. 5123-1**

- Convenient on/off rocker style switch that functions just like current indoor decorator style switches
- The internal elastomer membrane provides weatherproof protection
- The weatherproof decorator covers are compatible with single pole or 3-way decorator switches
- The decorator covers and the decorator switch and covers also includes the hardware pack and a weatherproof gasket



**2-Gang Decorator Switch Cover**

**Cat. No. 5127-1**

- Convenient on/off rocker style switch that functions just like current indoor decorator style switches
- The internal elastomer membrane provides weatherproof protection
- The weatherproof decorator covers are compatible with single pole or 3-way decorator switches
- The decorator covers and the decorator switch and covers also includes the hardware pack and a weatherproof gasket



**3-Gang Decorator Switch Cover**

**Cat. No. 5129-1**

- Convenient on/off rocker style switch that functions just like current indoor decorator style switches
- The internal elastomer membrane provides weatherproof protection
- The weatherproof decorator covers are compatible with single pole or 3-way decorator switches
- The decorator covers and the decorator switch and covers also includes the hardware pack and a weatherproof gasket



**COMMERCIAL CONSTRUCTION**



# Nonmetallic Covers



## Nonmetallic Blank Covers

**Cat. No. PBC100WH / PBC200WH / PBC300WH**

- Durable high impact polycarbonate construction
- Vertical or horizontal mount (Single Gang ONLY)
- Installation hardware, gasket included



## Nonmetallic Toggle/Device Covers

**Cat. No. PTC100WH**

- Durable high-impact polycarbonate construction
- Patented horseshoe adapter ensures a snug fit for small and large head switches
- Attached gasket and mounting hardware included
- Vertical mount



## Nonmetallic Toggle/Device Covers

**Cat. No. PTC521WH**

- Durable high-impact polycarbonate construction
- Patented horseshoe adapter ensures a snug fit for small and large head switches
- Patented Universal Fit Adapter System Technology (U-Fast) for 8-in-1 custom device configurations, comes pre-configured for GFCI
- Vertical Mount



## Nonmetallic Lamp holder Covers

**Cat. No. PLV330WH**

- Durable high impact polycarbonate construction
- Includes gasket and mounting hardware
- Attached gasket
- 2 closure plugs included



**COMMERCIAL CONSTRUCTION**





# Q & A Session

## ***Weatherproof Bell – TayMac Contact Information:***

**Agus The**

*WP Bell-TayMac Brand Manager*



480.225.9033 (Mobile)



[Athe@Hubbell.com](mailto:Athe@Hubbell.com)

**Eugene Hardin II**

*WP Bell-TayMac Product Manager*



480.389.7309 (Mobile)



[Ehardin@Hubbell.com](mailto:Ehardin@Hubbell.com)



**COMMERCIAL CONSTRUCTION**

