
BRYANT®



USB Charger Devices

Lead the Charge with Bryant® USB Devices





The Next Generation in **Charging Technology**



Charges a Wide Variety of Personal Mobile Devices



Great for Use in a Wide **Variety of Applications**



More Ways to Charge Faster with 5 Amp Devices



USB Charging ReceptaclesType-C • Type A&C • Type A

Bryant USB Chargers are available in the new Type-C port, a combination unit with Type A and C, and the legacy Type A, all with more power. The increase in power to a 5 Amp, 5 Volt USB port adds capacity so that there is always ample current to support multiple device charging. Portable mobile device manufacturers recently announced products using the faster Type-C ports. More phones, tablets and other electronic devices are expected to use this new standard.

The USB Charger delivers USB power eliminating the need for adapters, while maintaining electrical outlets for higher current requirements. The new USB standard Type-C port supports faster mobile device charging. Bryant offers more charging options with Type-C and Type A USB configurations.



Features

- Compliant with USB BC1.2 Battery Charging and 3.0 Power delivery.
 Compatible with USB 2.0, 3.0 and 3.1 devices.
- USB Type-C port is legacy USB Type A compatible (with adapter cord not included).
- Heavy duty stainless steel USB ports; rated for 10,000 cord insertions and removals.
- Patented Bryant Tamper-Resistant technology uses cam action shutters. When two plug blades are
 inserted the interlocked cams slide an insulating barrier out of the way. The friction-free design of the
 mechanism doors requires much less force, allowing the plug to slide in effortlessly.
- Designed for commercial, industrial and home use.

Metal PlugTrak® with USB Charger Outlets

Bryant PlugTrak® with USB Charger Outlets makes portable power and USB charging available and accessible. PlugTrak can be mounted on walls, under raised floors, over ceilings, or under cabinets making it perfect for both residential and commercial environments. Featuring tamper-resistant electrical wiring receptacles and USB outlets, PlugTrak® provides a quick and convenient place to charge.

Features

- 2.4 Amp, 5 Volt DC USB type 2.0 ports
- 15 Amp, 125 Volt AC tamper-resistant receptacles
- Three and six foot configurations
- cULus listed to UL5 Steel, UL1363 Portable Plug-in, and UL1310
- Green LED indicators light up to show USB power is available
- USB stainless steel ports rated for minimum 10,000 insertions and removals
- Complies with battery charging specification BC1.2
- Compatible with USB 1.1/2.0/3.0 devices



BRYANT® USB Charging Devices







USB Charging Receptacles

Type-C • Type A&C • Type A Standard and Hospital Grade





USB Charger Type-C

		USB with Commercial Grade Duplex		USB with Hospital Grade Duplex	
Description	Color	15A 125V	20A 125V	15A 125V	20A 125V
USB Charger Outlet:	Black	USBB15C5BK	USBB20C5BK	USBB8200C5BK	USBB8300C5BK
(2) Type-C port configurations,	Brown	USBB15C5	USBB20C5	USBB8200C5	USBB8300C5
high power 5 Amp, 5 Volt DC USB	Gray	USBB15C5GY	USBB20C5GY	USBB8200C5GY	USBB8300C5GY
output, USB ports rated 10,000 cycles	lvory	USBB15C5I	USBB20C5I	USBB8200C5I	USBB8300C5I
Tamper-Resistant duplex receptacle	Light Almond	USBB15C5LA	USBB20C5LA	USBB8200C5LA	USBB8300C5LA
	Red	_	_	USBB8200C5R	USBB8300C5R
	White	USBB15C5W	USBB20C5W	USBB8200C5W	USBB8300C5W





USB Charger Combination Type A&C

		USB with Commercial Grade Duplex		USB with Hospital Grade Duplex	
Description	Color	15A 125V	20A 125V	15A 125V	20A 125V
USB Charger Outlet:	Black	USBB15AC5BK	USBB20AC5BK	USBB8200AC5BK	USBB8300AC5BK
(1) Type A and (1) Type-C port	Brown	USBB15AC5	USBB20AC5	USBB8200AC5	USBB8300AC5
configurations,	Gray	USBB15AC5GY	USBB20AC5GY	USBB8200AC5GY	USBB8300AC5GY
high power 5 Amp, 5 Volt DC USB	lvory	USBB15AC5I	USBB20AC5I	USBB8200AC5I	USBB8300AC5I
output, USB ports rated 10,000 cycles	Light Almond	USBB15AC5LA	USBB20AC5LA	USBB8200AC5LA	USBB8300AC5LA
Tamper-Resistant duplex receptacle	Red	_	_	USBB8200AC5R	USBB8300AC5R
	White	USBB15AC5W	USBB20AC5W	USBB8200AC5W	USBB8300AC5W





USB Charger Type A

		USB with Commercial Grade Duplex		USB with Hospital Grade Duplex	
Description	Color	15A 125V	20A 125V	15A 125V	20A 125V
USB Charger Outlet:	Black	USBB15A5BK	USBB20A5BK	USBB8200A5BK	USBB8300A5BK
(2) Type A port configurations,	Brown	USBB15A5	USBB20A5	USBB8200A5	USBB8300A5
high power 5 Amp, 5 Volt DC USB	Gray	USBB15A5GY	USBB20A5GY	USBB8200A5GY	USBB8300A5GY
output, USB ports rated 10,000 cycles	lvory	USBB15A5I	USBB20A5I	USBB8200A5I	USBB8300A5I
Tamper-Resistant duplex receptacle	Light Almond	USBB15A5LA	USBB20A5LA	USBB8200A5LA	USBB8300A5LA
	Red	_	_	USBB8200A5R	USBB8300A5R
	White	USBB15A5W	USBB20A5W	USBB8200A5W	USBB8300A5W



USB Charger Outlets

- Four or Two USB ports, 5V DC, type A, class 2.0.
- Switch activated port door; when open enables power.
 When closed, all power is switched off, for a "zero" no-load draw.
- Shallow depth design for two port.
- 4 port USB cETLus listed to UL1310.
- 2 port USB cULus listed to UL1310.



.00

Description	Color	4 Port, 5 Amp	2 Port, 3 Amp
USB Charger Outlets,	Black	USBB4BK	USBB2BK
USB Type 2.0 Ports,	Brown	USBB4	USBB2
5 Volt DC, Decorator Style	Gray	USBB4GY	USBB2GY
	lvory	USBB4I	USBB2I
	Light Almond	USBB4LA	USBB2LA
	White	USBB4W	USBB2W



Switch Combo Outlets

- Two USB ports, 5V DC, type A, class 2.0.
- Isolated 15 Amp, 120V AC single pole/3-way switch.
- cULus listed to UL20 and UL1310.

Description	Color	Catalog Number
Switch Combo Outlet, two USB Type 2.0 Ports, 2.1 Amp,	Black Brown	USBB102BK USBB102
5 Volt DC, Decorator Style	Gray	USBB102GY
	lvory Light Almond	USBB102I USBB102LA
	White	USBB102W





- USB type 2.0 ports, 2.4 Amp, 5 Volt DC.
- 15 Amp, 125 Volt AC receptacles.

Material	Length	Ends	# of USB Ports	# of Single Receptacles	Color	Catalog Number
Steel	3 feet	6 inch leads	2	2	lvory	HBL20GB312UIV
Steel	6 feet	6 inch leads	4	4	lvory	HBL20GB612UIV



