


SERIES H and E-Z HOSE REELS HEAVY DUTY FOR MACHINE PULL or E-Z PULL FOR GENTLE HAND PULL

Heavy duty hose reels are designed for supplying air or fluid to machines in applications where the machine supplies the power to pull out the hose and the reel supplies the rewinding power. They are also widely used overhead where the hose is pulled down by hand. In hand pull applications, a ratchet lock is usually employed to keep the hose extended while in use.

E-Z PULL[™] REELS are designed to make hose handling safer and smoother and to minimize costly replacement caused by excessive rewind speeds. Rewind pull is kept to a minimum resulting in a reel that is gentle to pull out, yet very adequate to rewind the hose. In some situations, the rewind pull provided by E-Z PULL[™] reels may require a gentle assist from the operator. E-Z PULL[™] reels should be mounted a maximum 3 ft.(0.9m) above the floor so that the hose may be pulled horizontally. Typical mounting is under a workbench.

BOTH REELS FEATURE:

- 1/4", 3/8", or 1/2" (6, 9, 13mm) hose
- All welded solid steel construction
- · Fully automatic; Machine mountable
- Heavy duty mounting bracket
- Safetychange® spring motor
- Weatherproof gasket on spring motor
- Positive ratchet lock with disengage
- Multi-position adjustable hose guide
- Orange polyester baked-on finish
- Adjustable hose stop included
- Optional 340° pivot base



SERIES "H" APPLICATION:

- · Connect machines to air/water supply.
- Hand pull, with or without ratchet stop. Ideal for fluids, compressed air.
- Mount base up, down or to wall for vertical or horizontal hose travel.
- Add optional 340° pivot base. Reel turns to follow hose pay-out.


E-Z PULL[™] APPLICATION:

- Mount under workbench or low on wall.
- Supply air to tools, compressed air for inflating or cleaning.
- Increase safety...hose does not "fly back" to reel.

HOSE DATA				MACHINE USE		E-Z PULL FOR				
INSIDE DIA. in. (mm)	INPUT & OUTPUT FITTINGS	MAX LENGTH ft. (m)	MAX PRES. psi (N/mm ²)	OR OVERHEAD MOUNTED HAND PULL -MODEL NO	REEL SIZE	HORIZONTAL HAND PULL APPLICATIONS –MODEL NO.–	REEL SIZE	NET WEIGHT Ibs. (kg)	HOSE STOP	340 [°] BASE (OPT)
1/4 (6)	0.25 NPTF	25 (7.5)	315 (2.17)	HC2525	A	EZ4-2525	AB	00 (10)	CP-2	PB14
		35 (10.5)		HC2535		EZ4-2535		30 (13)		
		50 (15.0)		HE2550		EZ9-2550		42 (19)		
3/8 (9)	0.38 NPTF	25 (7.5)		HC3825		EZ4-3825	A	30 (13)		
		35 (10.5)		HD3835		EZ4-3835		30 (13)		
		50 (15.0)		HF3850	В	EZ9-3850	В	60 (27)		PB19
1/2 (13)	0.50 NPTF	25 (7.5)		HG5025		EZ9-5025			CP-3	
		35 (10.5)		HG5035		EZ9-5035		62 (28)		
		50 (15.0)		HG5050		EZ9-5050				

REEL AND PIVOT BASE DIMENSIONS

All dimensions in inches. For millimeters, multiply inches by 25.4.





Gleason Reel Corp.

600 South Clark St. Mayville, WI 53050 Phone: 920-387-4120 Fax: 920-387-4189 www.hubbell-gleason.com